

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P770838

Luminaire Tested: LD6D70BD010-EU6DR6570959027-6LBS1MW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P770838
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D70BD010-EU6DR6570959027-6LBS1MW
Description: 6 INCH ROUND SHALLOW MATTE WHITE TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6867.0 lumens
Efficiency: N/A
Efficacy: 103.1 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct

Input Watts (W): 66.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P770838

CATALOG NUMBER: LD6D70BD010-EU6DR6570959027-6LBS1MW

Luminous Intensity Polar Plot





TEST NUMBER: P770838

CATALOG NUMBER: LD6D70BD010-EU6DR6570959027-6LBS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	364148
5°	363229
10°	362922
15°	351732
20°	320208
25°	279045
30°	232085
35°	183892
40°	132728
45°	83851
50°	43704
55°	23226
60°	12206
65°	6716
70°	2818
75°	3091
80°	2153
85°	1809

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 83851 cd/sqm



TEST NUMBER: P770838

CATALOG NUMBER: LD6D70BD010-EU6DR6570959027-6LBS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	589.6	8.6
10°-20°	1614.6	23.5
20°-30°	1973.6	28.7
30°-40°	1601.4	23.3
40°-50°	798.0	11.6
50°-60°	222.6	3.2
60°-70°	50.6	0.7
70°-80°	13.2	0.2
80°-90°	3.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4177.9	60.8
0°-40°	5779.3	84.2
0°-60°	6799.9	99.0
0°-90°	6867.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6867.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6235	
5°	6196	590
15°	5817	1615
25°	4330	1974
35°	2579	1601
45°	1015	798
55°	228	223
65°	49	51
75°	14	13
85°	3	3
90°	0	



TEST NUMBER: P770838

CATALOG NUMBER: LD6D70BD010-EU6DR6570959027-6LBS1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	6235.0
2.5°	6230.4
5°	6195.6
7.5°	6175.5
10°	6119.6
12.5°	6006.0
15°	5817.2
17.5°	5522.2
20°	5152.0
22.5°	4752.5
25°	4330.2
27.5°	3878.4
30°	3441.4
32.5°	3009.9
35°	2579.2
37.5°	2149.5
40°	1740.9
42.5°	1357.9
45°	1015.2
47.5°	707.3
50°	481.0
52.5°	331.7
55°	228.1
57.5°	153.9
60°	104.5
62.5°	72.4
65°	48.6
67.5°	24.7
70°	16.5
72.5°	15.6
75°	13.7
77.5°	9.2
80°	6.4
82.5°	4.6
85°	2.7
87.5°	1.8
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)