

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P770909

Luminaire Tested: LD6D70BD010-EU6DR7070959027-6LBDP1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P770909
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D70BD010-EU6DR7070959027-6LBDP1B
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4601.4 lumens
Efficiency: N/A
Efficacy: 69.1 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 66.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P770909
CATALOG NUMBER: LD6D70BD010-EU6DR7070959027-6LBDP1B

Luminous Intensity Polar Plot





TEST NUMBER: P770909

CATALOG NUMBER: LD6D70BD010-EU6DR7070959027-6LBDP1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	565239
5°	548445
10°	533163
15°	526166
20°	491334
25°	369106
30°	260931
35°	92421
40°	48594
45°	51764
50°	53595
55°	54614
60°	54958
65°	53775
70°	50762
75°	47028
80°	41716
85°	33848

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 54966 cd/sqm



TEST NUMBER: P770909

CATALOG NUMBER: LD6D70BD010-EU6DR7070959027-6LBDP1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	471.7	10.3
10°-20°	1293.7	28.1
20°-30°	1424.9	31.0
30°-40°	544.4	11.8
40°-50°	257.0	5.6
50°-60°	255.6	5.6
60°-70°	204.6	4.4
70°-80°	117.6	2.6
80°-90°	31.9	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3190.3	69.3
0°-40°	3734.6	81.2
0°-60°	4247.2	92.3
0°-90°	4601.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4601.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5173	
5°	5000	472
15°	4652	1294
25°	3062	1425
35°	693	544
45°	335	257
55°	287	256
65°	208	205
75°	111	118
85°	27	32
90°	0	



TEST NUMBER: P770909

CATALOG NUMBER: LD6D70BD010-EU6DR7070959027-6LBDP1B

CANDELA DISTRIBUTION (FULL):

0°	
0°	5173.3
2.5°	5119.3
5°	5000.5
7.5°	4901.4
10°	4805.6
12.5°	4724.5
15°	4651.6
17.5°	4475.5
20°	4225.7
22.5°	3686.7
25°	3061.7
27.5°	2665.3
30°	2068.2
32.5°	1335.9
35°	692.9
37.5°	374.3
40°	340.7
42.5°	338.3
45°	335.0
47.5°	327.6
50°	315.3
52.5°	301.4
55°	286.7
57.5°	270.3
60°	251.5
62.5°	230.2
65°	208.0
67.5°	183.5
70°	158.9
72.5°	134.3
75°	111.4
77.5°	87.6
80°	66.3
82.5°	46.7
85°	27.0
87.5°	10.6
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)