

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P770768

Luminaire Tested: LD6D70BD010-EU6DR6070959030-6LBDP1LI

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P770768  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD6D70BD010-EU6DR6070959030-6LBDP1LI  
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 60° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 8499.3 lumens  
Efficiency: N/A  
Efficacy: 127.6 lumens/watt  
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 66.6  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight

TEST NUMBER: P770768

CATALOG NUMBER: LD6D70BD010-EU6DR6070959030-6LBDP1LI

### Luminous Intensity Polar Plot





TEST NUMBER: P770768

CATALOG NUMBER: LD6D70BD010-EU6DR6070959030-6LBDP1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93			93																
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86			86																
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80			80																
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75			75																
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70			70																
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66			66																
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62			62																
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59			59																
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55			55																
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53			53																

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1102878
5°	1130003
10°	1143645
15°	1089479
20°	960588
25°	776947
30°	525546
35°	263351
40°	42718
45°	41813
50°	42648
55°	43298
60°	44491
65°	45502
70°	46577
75°	47154
80°	45492
85°	37860

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 75°  
 Luminance: 47154 cd/sqm



TEST NUMBER: P770768

CATALOG NUMBER: LD6D70BD010-EU6DR6070959030-6LBDP1LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	984.7	11.6
10°-20°	2664.2	31.3
20°-30°	2866.4	33.7
30°-40°	1246.0	14.7
40°-50°	209.3	2.5
50°-60°	203.5	2.4
60°-70°	174.0	2.0
70°-80°	116.5	1.4
80°-90°	34.8	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6515.3	76.7
0°-40°	7761.2	91.3
0°-60°	8174.0	96.2
0°-90°	8499.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8499.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	10094	
5°	10303	985
15°	9632	2664
25°	6445	2866
35°	1974	1246
45°	271	209
55°	227	203
65°	176	174
75°	112	116
85°	30	35
90°	0	



TEST NUMBER: P770768

CATALOG NUMBER: LD6D70BD010-EU6DR6070959030-6LBDP1LI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	10094.0
2.5°	10377.8
5°	10302.9
7.5°	10326.5
10°	10308.1
12.5°	10095.3
15°	9631.6
17.5°	9009.0
20°	8261.5
22.5°	7461.5
25°	6444.7
27.5°	5154.7
30°	4165.6
32.5°	3210.5
35°	1974.4
37.5°	844.7
40°	299.5
42.5°	275.9
45°	270.6
47.5°	261.4
50°	250.9
52.5°	239.1
55°	227.3
57.5°	215.4
60°	203.6
62.5°	190.5
65°	176.0
67.5°	161.6
70°	145.8
72.5°	128.7
75°	111.7
77.5°	92.0
80°	72.3
82.5°	51.2
85°	30.2
87.5°	10.5
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)