

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P770560

Luminaire Tested: LD6D70BD010-EU6DR4570959040-6LBDP1LI

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P770560
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-36)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D70BD010-EU6DR4570959040-6LBDP1LI
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 45° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9182.0 lumens
Efficiency: N/A
Efficacy: 137.9 lumens/watt
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.69
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 66.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P770560
CATALOG NUMBER: LD6D70BD010-EU6DR4570959040-6LBDP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P770560

CATALOG NUMBER: LD6D70BD010-EU6DR4570959040-6LBDP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	98	98	97	95					95			
2	109	105	102	99	107	103	100	98	100	98	95	97	95	93	95	93	91	90					90			
3	105	99	95	91	103	98	94	91	95	92	89	93	90	88	91	89	87	85					85			
4	100	94	89	85	99	93	88	85	91	87	84	89	86	83	87	84	82	81					81			
5	96	89	84	80	95	88	83	80	86	82	79	85	81	79	83	80	78	77					77			
6	92	85	80	76	91	84	79	76	83	78	75	81	77	75	80	77	74	73					73			
7	89	81	75	72	87	80	75	72	79	74	71	78	74	71	77	73	71	69					69			
8	85	77	72	68	84	76	71	68	75	71	68	74	70	67	73	70	67	66					66			
9	82	73	68	65	81	73	68	65	72	68	65	71	67	64	71	67	64	63					63			
10	79	70	65	62	78	70	65	62	69	65	62	68	64	61	68	64	61	60					60			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1773236
5°	1722747
10°	1648207
15°	1508457
20°	1196727
25°	747133
30°	411798
35°	184909
40°	72827
45°	34318
50°	16267
55°	8515
60°	4174
65°	982
70°	415
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 34318 cd/sqm



TEST NUMBER: P770560

CATALOG NUMBER: LD6D70BD010-EU6DR4570959040-6LBDP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1475.8	16.1
10°-20°	3632.2	39.6
20°-30°	2876.4	31.3
30°-40°	957.9	10.4
40°-50°	190.1	2.1
50°-60°	43.2	0.5
60°-70°	6.2	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	7984.5	87.0
0°-40°	8942.3	97.4
0°-60°	9175.6	99.9
0°-90°	9182.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	9182.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	16229	
5°	15707	###
15°	13336	3632
25°	6197	2876
35°	1386	958
45°	222	190
55°	45	43
65°	4	6
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P770560

CATALOG NUMBER: LD6D70BD010-EU6DR4570959040-6LBDP1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	16229.4
2.5°	16123.4
5°	15707.3
7.5°	15363.9
10°	14855.9
12.5°	14179.3
15°	13335.6
17.5°	12066.7
20°	10292.4
22.5°	8178.5
25°	6197.4
27.5°	4537.9
30°	3264.0
32.5°	2219.8
35°	1386.3
37.5°	822.1
40°	510.6
42.5°	335.7
45°	222.1
47.5°	143.0
50°	95.7
52.5°	63.8
55°	44.7
57.5°	29.4
60°	19.1
62.5°	10.2
65°	3.8
67.5°	1.3
70°	1.3
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)