

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P768518

Luminaire Tested: LD6D55D010-EU6DR6555659035-6LBDP1H

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P768518
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D55D010-EU6DR6555659035-6LBDP1H
Description: 6 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5765.4 lumens
Efficiency: N/A
Efficacy: 99.1 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 58.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P768518
CATALOG NUMBER: LD6D55D010-EU6DR6555659035-6LBDP1H

Luminous Intensity Polar Plot





TEST NUMBER: P768518
 CATALOG NUMBER: LD6D55D010-EU6DR6555659035-6LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93		
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87		
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80		
4	97	89	84	79	95	88	83	79	86	82	78	84	80	77	82	79	76	75		
5	92	83	78	73	90	83	77	73	81	76	72	79	75	72	77	74	71	69		
6	87	78	72	68	86	77	72	68	76	71	67	74	70	67	73	69	66	65		
7	83	73	67	63	81	73	67	63	71	66	62	70	66	62	69	65	62	60		
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	57		
9	75	65	59	55	74	65	59	55	64	58	55	63	58	55	62	58	54	53		
10	71	61	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	620219
5°	620723
10°	642579
15°	643647
20°	592585
25°	504912
30°	386527
35°	273075
40°	161186
45°	65438
50°	23729
55°	13220
60°	7583
65°	4162
70°	4377
75°	3419
80°	3524
85°	3009

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 65438 cd/sqm



TEST NUMBER: P768518

CATALOG NUMBER: LD6D55D010-EU6DR6555659035-6LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	546.6	9.5
10°-20°	1576.7	27.3
20°-30°	1891.7	32.8
30°-40°	1271.3	22.1
40°-50°	380.6	6.6
50°-60°	67.2	1.2
60°-70°	19.1	0.3
70°-80°	9.4	0.2
80°-90°	2.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4015.0	69.6
0°-40°	5286.3	91.7
0°-60°	5734.0	99.5
0°-90°	5765.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5765.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5676	
5°	5660	547
15°	5690	1577
25°	4188	1892
35°	2047	1271
45°	424	381
55°	69	67
65°	16	19
75°	8	9
85°	2	3
90°	0	



TEST NUMBER: P768518

CATALOG NUMBER: LD6D55D010-EU6DR6555659035-6LBDP1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	5676.5
2.5°	5700.7
5°	5659.5
7.5°	5745.0
10°	5791.8
12.5°	5780.5
15°	5690.2
17.5°	5469.2
20°	5096.5
22.5°	4657.7
25°	4188.2
27.5°	3658.2
30°	3063.7
32.5°	2524.9
35°	2047.3
37.5°	1575.4
40°	1130.1
42.5°	738.1
45°	423.5
47.5°	224.3
50°	139.6
52.5°	96.8
55°	69.4
57.5°	50.0
60°	34.7
62.5°	22.6
65°	16.1
67.5°	14.5
70°	13.7
72.5°	10.5
75°	8.1
77.5°	7.3
80°	5.6
82.5°	4.0
85°	2.4
87.5°	1.6
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)