

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P770883

Luminaire Tested: LD6D70BD010-EU6DR6570959050-6LBDP1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P770883
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D70BD010-EU6DR6570959050-6LBDP1B
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5612.7 lumens
Efficiency: N/A
Efficacy: 84.3 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 66.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P770883

CATALOG NUMBER: LD6D70BD010-EU6DR6570959050-6LBDP1B

Luminous Intensity Polar Plot





TEST NUMBER: P770883
 CATALOG NUMBER: LD6D70BD010-EU6DR6570959050-6LBDP1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93																			
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87																			
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80																			
4	97	89	84	79	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	83	78	73	90	83	77	73	81	76	72	79	75	72	77	74	71	69																			
6	87	78	72	68	86	77	72	68	76	71	67	74	70	67	73	69	66	65																			
7	83	73	67	63	81	73	67	63	71	66	62	70	66	62	69	65	62	60																			
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	57																			
9	75	65	59	55	74	65	59	55	64	58	55	63	58	55	62	58	54	53																			
10	71	61	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	603786
5°	604283
10°	625559
15°	626590
20°	576888
25°	491531
30°	376282
35°	265845
40°	156921
45°	63708
50°	23100
55°	12858
60°	7386
65°	4059
70°	4249
75°	3335
80°	3461
85°	3009

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 63708 cd/sqm



TEST NUMBER: P770883

CATALOG NUMBER: LD6D70BD010-EU6DR6570959050-6LBDP1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	532.1	9.5
10°-20°	1534.9	27.3
20°-30°	1841.6	32.8
30°-40°	1237.6	22.1
40°-50°	370.5	6.6
50°-60°	65.4	1.2
60°-70°	18.6	0.3
70°-80°	9.1	0.2
80°-90°	2.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3908.6	69.6
0°-40°	5146.3	91.7
0°-60°	5582.1	99.5
0°-90°	5612.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5612.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5526	
5°	5510	532
15°	5539	1535
25°	4077	1842
35°	1993	1238
45°	412	370
55°	68	65
65°	16	19
75°	8	9
85°	2	3
90°	0	



TEST NUMBER: P770883

CATALOG NUMBER: LD6D70BD010-EU6DR6570959050-6LBDP1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	5526.1
2.5°	5549.6
5°	5509.6
7.5°	5592.8
10°	5638.4
12.5°	5627.4
15°	5539.4
17.5°	5324.3
20°	4961.5
22.5°	4534.3
25°	4077.2
27.5°	3561.3
30°	2982.5
32.5°	2458.0
35°	1993.1
37.5°	1533.7
40°	1100.2
42.5°	718.5
45°	412.3
47.5°	218.3
50°	135.9
52.5°	94.2
55°	67.5
57.5°	48.7
60°	33.8
62.5°	22.0
65°	15.7
67.5°	14.1
70°	13.3
72.5°	10.2
75°	7.9
77.5°	7.1
80°	5.5
82.5°	3.9
85°	2.4
87.5°	1.6
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)