

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P770963

Luminaire Tested: LD6D70BD010-EU6DR7070959050-6LBDP1LI

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P770963  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD6D70BD010-EU6DR7070959050-6LBDP1LI  
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 70° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 9114.0 lumens  
Efficiency: N/A  
Efficacy: 136.8 lumens/watt  
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct


Input Watts (W): 66.6  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



Downlight

TEST NUMBER: P770963  
CATALOG NUMBER: LD6D70BD010-EU6DR7070959050-6LBDP1LI

### Luminous Intensity Polar Plot





TEST NUMBER: P770963  
 CATALOG NUMBER: LD6D70BD010-EU6DR7070959050-6LBDP1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1119573
5°	1086296
10°	1056020
15°	1042163
20°	973169
25°	731087
30°	516816
35°	183068
40°	96261
45°	102523
50°	106169
55°	108160
60°	108846
65°	106541
70°	100533
75°	93127
80°	82678
85°	67069

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 57.5°  
 Luminance: 108874 cd/sqm



TEST NUMBER: P770963

CATALOG NUMBER: LD6D70BD010-EU6DR7070959050-6LBDP1LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	934.2	10.3
10°-20°	2562.5	28.1
20°-30°	2822.2	31.0
30°-40°	1078.3	11.8
40°-50°	509.1	5.6
50°-60°	506.2	5.6
60°-70°	405.3	4.4
70°-80°	232.9	2.6
80°-90°	63.3	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6318.9	69.3
0°-40°	7397.2	81.2
0°-60°	8412.5	92.3
0°-90°	9114.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	9114.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	10247	
5°	9904	934
15°	9213	2562
25°	6064	2822
35°	1372	1078
45°	664	509
55°	568	506
65°	412	405
75°	221	233
85°	54	63
90°	0	



TEST NUMBER: P770963

CATALOG NUMBER: LD6D70BD010-EU6DR7070959050-6LBDP1LI

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	10246.8
2.5°	10139.7
5°	9904.4
7.5°	9708.1
10°	9518.3
12.5°	9357.7
15°	9213.3
17.5°	8864.5
20°	8369.7
22.5°	7302.2
25°	6064.3
27.5°	5279.1
30°	4096.4
32.5°	2646.1
35°	1372.5
37.5°	741.4
40°	674.9
42.5°	670.0
45°	663.5
47.5°	648.9
50°	624.6
52.5°	597.0
55°	567.8
57.5°	535.4
60°	498.1
62.5°	455.9
65°	412.1
67.5°	363.4
70°	314.7
72.5°	266.1
75°	220.6
77.5°	173.6
80°	131.4
82.5°	92.5
85°	53.5
87.5°	21.1
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)