

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P768466

Luminaire Tested: LD6D55D010-EU6DR6055659050-6LBDP1H

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P768466
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D55D010-EU6DR6055659050-6LBDP1H
Description: 6 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6956.2 lumens
Efficiency: N/A
Efficacy: 119.5 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 58.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P768466
CATALOG NUMBER: LD6D55D010-EU6DR6055659050-6LBDP1H

Luminous Intensity Polar Plot





TEST NUMBER: P768466

CATALOG NUMBER: LD6D55D010-EU6DR6055659050-6LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100															
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93				93															
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86				86															
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80				80															
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75				75															
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70				70															
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66				66															
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62				62															
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59				59															
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55				55															
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53				53															

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	902636
5°	924839
10°	936009
15°	891675
20°	786179
25°	635884
30°	430116
35°	215533
40°	34959
45°	34226
50°	34914
55°	35431
60°	36406
65°	37255
70°	38111
75°	38585
80°	37186
85°	30965

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 75°
 Luminance: 38585 cd/sqm



TEST NUMBER: P768466

CATALOG NUMBER: LD6D55D010-EU6DR6055659050-6LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	805.9	11.6
10°-20°	2180.5	31.3
20°-30°	2346.0	33.7
30°-40°	1019.7	14.7
40°-50°	171.3	2.5
50°-60°	166.5	2.4
60°-70°	142.4	2.0
70°-80°	95.3	1.4
80°-90°	28.5	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5332.3	76.7
0°-40°	6352.1	91.3
0°-60°	6689.9	96.2
0°-90°	6956.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6956.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8261	
5°	8432	806
15°	7883	2180
25°	5275	2346
35°	1616	1020
45°	222	171
55°	186	167
65°	144	142
75°	91	95
85°	25	28
90°	0	



TEST NUMBER: P768466

CATALOG NUMBER: LD6D55D010-EU6DR6055659050-6LBDP1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	8261.3
2.5°	8493.6
5°	8432.3
7.5°	8451.6
10°	8436.6
12.5°	8262.4
15°	7882.9
17.5°	7373.3
20°	6761.5
22.5°	6106.8
25°	5274.6
27.5°	4218.8
30°	3409.2
32.5°	2627.6
35°	1615.9
37.5°	691.3
40°	245.1
42.5°	225.8
45°	221.5
47.5°	214.0
50°	205.4
52.5°	195.7
55°	186.0
57.5°	176.3
60°	166.6
62.5°	155.9
65°	144.1
67.5°	132.2
70°	119.3
72.5°	105.4
75°	91.4
77.5°	75.3
80°	59.1
82.5°	41.9
85°	24.7
87.5°	8.6
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)