

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P770967

Luminaire Tested: LD6D70BD010-EU6DR7070959050-6LBS1LI

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P770967
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-76)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D70BD010-EU6DR7070959050-6LBS1LI
Description: 6 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9593.7 lumens
Efficiency: N/A
Efficacy: 144.0 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.04
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 66.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P770967
CATALOG NUMBER: LD6D70BD010-EU6DR7070959050-6LBS1LI

Luminous Intensity Polar Plot





TEST NUMBER: P770967

CATALOG NUMBER: LD6D70BD010-EU6DR7070959050-6LBS1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	95	94	93																			
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85																			
3	101	94	88	84	99	92	87	83	90	85	82	87	84	81	85	82	79	78																			
4	95	87	81	76	93	86	80	76	83	78	75	81	77	74	79	76	73	71																			
5	89	80	74	69	88	79	73	69	78	72	68	76	71	68	74	70	67	65																			
6	84	75	68	63	83	74	68	63	72	67	63	71	66	62	69	65	62	60																			
7	80	69	63	58	78	69	62	58	67	62	58	66	61	57	65	61	57	56																			
8	75	65	58	54	74	64	58	54	63	57	53	62	57	53	61	56	53	51																			
9	71	61	54	50	70	60	54	50	59	53	50	58	53	49	57	53	49	48																			
10	67	57	50	46	66	56	50	46	55	50	46	55	50	46	54	49	46	44																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	827344
5°	825273
10°	823488
15°	823251
20°	815212
25°	765783
30°	682696
35°	544322
40°	361424
45°	216078
50°	112017
55°	58881
60°	20825
65°	362
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 216078 cd/sqm



TEST NUMBER: P770967

CATALOG NUMBER: LD6D70BD010-EU6DR7070959050-6LBS1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	715.6	7.5
10°-20°	2052.3	21.4
20°-30°	2895.2	30.2
30°-40°	2499.3	26.1
40°-50°	1119.2	11.7
50°-60°	293.0	3.1
60°-70°	19.1	0.2
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5663.0	59.0
0°-40°	8162.3	85.1
0°-60°	9574.6	99.8
0°-90°	9593.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	9593.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7572	
5°	7524	716
15°	7278	2052
25°	6352	2895
35°	4081	2499
45°	1398	1119
55°	309	293
65°	1	19
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P770967

CATALOG NUMBER: LD6D70BD010-EU6DR7070959050-6LBS1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	7572.2
2.5°	7564.0
5°	7524.5
7.5°	7491.8
10°	7422.4
12.5°	7359.7
15°	7278.0
17.5°	7184.1
20°	7011.2
22.5°	6726.6
25°	6352.1
27.5°	5917.7
30°	5411.2
32.5°	4791.7
35°	4080.9
37.5°	3296.6
40°	2534.0
42.5°	1925.4
45°	1398.4
47.5°	964.1
50°	659.0
52.5°	454.8
55°	309.1
57.5°	186.5
60°	95.3
62.5°	30.0
65°	1.4
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)