

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P769024

Luminaire Tested: LD6D60D010-EU6DR5055659024-6LBDP1B

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P769024  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-44)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD6D60D010-EU6DR5055659024-6LBDP1B  
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 50° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5675.2 lumens  
Efficiency: N/A  
Efficacy: 88.1 lumens/watt  
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.73  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct


Input Watts (W): 64.4  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



Downlight

TEST NUMBER: P769024  
CATALOG NUMBER: LD6D60D010-EU6DR5055659024-6LBDP1B

### Luminous Intensity Polar Plot





TEST NUMBER: P769024

CATALOG NUMBER: LD6D60D010-EU6DR5055659024-6LBDP1B

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100															
1	114	112	109	107	112	110	108	106	106	104	102	102	101	99	98	97	97	95				95															
2	109	105	101	98	107	103	100	97	100	98	95	97	95	93	95	93	91	90				90															
3	105	99	95	91	103	98	94	90	95	92	89	93	90	88	91	88	86	85				85															
4	100	94	89	85	99	93	88	85	90	87	84	89	85	83	87	84	82	80				80															
5	96	89	84	80	95	88	83	79	86	82	79	85	81	78	83	80	77	76				76															
6	92	84	79	75	91	83	79	75	82	78	74	81	77	74	79	76	74	72				72															
7	88	80	75	71	87	79	74	71	78	74	71	77	73	70	76	73	70	69				69															
8	85	76	71	67	84	76	71	67	75	70	67	74	70	67	73	69	66	65				65															
9	81	73	68	64	80	72	67	64	71	67	64	71	67	64	70	66	63	62				62															
10	78	70	64	61	77	69	64	61	68	64	61	68	64	61	67	63	60	59				59															

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	999102
5°	988628
10°	972344
15°	885397
20°	736751
25°	522984
30°	276815
35°	112802
40°	41890
45°	19176
50°	7870
55°	4115
60°	2032
65°	595
70°	0
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 19176 cd/sqm



TEST NUMBER: P769024

CATALOG NUMBER: LD6D60D010-EU6DR5055659024-6LBDP1B

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	852.0	15.0
10°-20°	2153.2	37.9
20°-30°	1934.1	34.1
30°-40°	605.6	10.7
40°-50°	106.0	1.9
50°-60°	21.1	0.4
60°-70°	3.2	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4939.3	87.0
0°-40°	5544.8	97.7
0°-60°	5672.0	99.9
0°-90°	5675.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5675.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	9144	
5°	9014	852
15°	7827	2153
25°	4338	1934
35°	846	606
45°	124	106
55°	22	21
65°	2	3
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P769024

CATALOG NUMBER: LD6D60D010-EU6DR5055659024-6LBDP1B

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	9144.2
2.5°	9098.7
5°	9013.9
7.5°	8884.4
10°	8764.1
12.5°	8378.7
15°	7827.4
17.5°	7127.4
20°	6336.4
22.5°	5421.3
25°	4338.1
27.5°	3189.4
30°	2194.1
32.5°	1428.6
35°	845.7
37.5°	485.7
40°	293.7
42.5°	191.2
45°	124.1
47.5°	75.6
50°	46.3
52.5°	31.6
55°	21.6
57.5°	14.6
60°	9.3
62.5°	5.4
65°	2.3
67.5°	0.8
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)