

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P771522

Luminaire Tested: LD6D75BD010-EU6DR6070959024-6LBDP1LI

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P771522
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D75BD010-EU6DR6070959024-6LBDP1LI
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7697.6 lumens
Efficiency: N/A
Efficacy: 106.3 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 72.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P771522

CATALOG NUMBER: LD6D75BD010-EU6DR6070959024-6LBDP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P771522

CATALOG NUMBER: LD6D75BD010-EU6DR6070959024-6LBDP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|---|-----|--|--|--|--|--|----|--|--|--|--|--|--|--|--|---|
| RF | 20 | | | | | | | | | 20 | | | | | | | | | 20 | | | | | | | | | 20 | | | | | | | | | |
| RC | 80 | | | | | | | | | 50 | | | | | | | | | 30 | | | | | | | | | 10 | | | | | | | | | 0 |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 | | | | | | | | | | | | | | | | |
| RCR | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | | | 100 | | | | | | | | | | | | | | | |
| 1 | 113 | 110 | 108 | 105 | 111 | 108 | 106 | 104 | 104 | 102 | 100 | 100 | 99 | 97 | 97 | 96 | 95 | 93 | | | | 93 | | | | | | | | | | | | | | | |
| 2 | 107 | 102 | 98 | 95 | 105 | 101 | 97 | 94 | 97 | 94 | 92 | 94 | 92 | 90 | 92 | 90 | 88 | 86 | | | | 86 | | | | | | | | | | | | | | | |
| 3 | 102 | 96 | 90 | 86 | 100 | 94 | 89 | 86 | 91 | 88 | 84 | 89 | 86 | 83 | 87 | 84 | 82 | 80 | | | | 80 | | | | | | | | | | | | | | | |
| 4 | 97 | 89 | 84 | 80 | 95 | 88 | 83 | 79 | 86 | 82 | 78 | 84 | 80 | 77 | 82 | 79 | 76 | 75 | | | | 75 | | | | | | | | | | | | | | | |
| 5 | 92 | 84 | 78 | 74 | 91 | 83 | 78 | 74 | 81 | 77 | 73 | 80 | 76 | 72 | 78 | 75 | 72 | 70 | | | | 70 | | | | | | | | | | | | | | | |
| 6 | 88 | 79 | 73 | 69 | 87 | 78 | 73 | 69 | 77 | 72 | 68 | 75 | 71 | 68 | 74 | 70 | 67 | 66 | | | | 66 | | | | | | | | | | | | | | | |
| 7 | 84 | 75 | 69 | 65 | 83 | 74 | 68 | 64 | 73 | 68 | 64 | 72 | 67 | 64 | 71 | 67 | 63 | 62 | | | | 62 | | | | | | | | | | | | | | | |
| 8 | 80 | 71 | 65 | 61 | 79 | 70 | 65 | 61 | 69 | 64 | 60 | 68 | 64 | 60 | 67 | 63 | 60 | 59 | | | | 59 | | | | | | | | | | | | | | | |
| 9 | 77 | 67 | 61 | 57 | 75 | 67 | 61 | 57 | 66 | 61 | 57 | 65 | 60 | 57 | 64 | 60 | 57 | 55 | | | | 55 | | | | | | | | | | | | | | | |
| 10 | 73 | 64 | 58 | 54 | 72 | 63 | 58 | 54 | 62 | 58 | 54 | 62 | 57 | 54 | 61 | 57 | 54 | 53 | | | | 53 | | | | | | | | | | | | | | | |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|---------|
| | 0° |
| 0° | 998851 |
| 5° | 1023406 |
| 10° | 1035772 |
| 15° | 986714 |
| 20° | 869977 |
| 25° | 703661 |
| 30° | 475964 |
| 35° | 238515 |
| 40° | 38695 |
| 45° | 37872 |
| 50° | 38619 |
| 55° | 39203 |
| 60° | 40295 |
| 65° | 41210 |
| 70° | 42200 |
| 75° | 42679 |
| 80° | 41150 |
| 85° | 34349 |

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 75°
 Luminance: 42679 cd/sqm



TEST NUMBER: P771522

CATALOG NUMBER: LD6D75BD010-EU6DR6070959024-6LBDP1LI

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 891.8 | 11.6 |
| 10°-20° | 2412.9 | 31.3 |
| 20°-30° | 2596.0 | 33.7 |
| 30°-40° | 1128.5 | 14.7 |
| 40°-50° | 189.5 | 2.5 |
| 50°-60° | 184.3 | 2.4 |
| 60°-70° | 157.6 | 2.0 |
| 70°-80° | 105.5 | 1.4 |
| 80°-90° | 31.5 | 0.4 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 5900.7 | 76.7 |
| 0°-40° | 7029.2 | 91.3 |
| 0°-60° | 7403.0 | 96.2 |
| 0°-90° | 7697.6 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 7697.6 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 9142 | |
| 5° | 9331 | 892 |
| 15° | 8723 | 2413 |
| 25° | 5837 | 2596 |
| 35° | 1788 | 1128 |
| 45° | 245 | 190 |
| 55° | 206 | 184 |
| 65° | 159 | 158 |
| 75° | 101 | 105 |
| 85° | 27 | 32 |
| 90° | 0 | |



TEST NUMBER: P771522

CATALOG NUMBER: LD6D75BD010-EU6DR6070959024-6LBDP1LI

CANDELA DISTRIBUTION (FULL):

| 0° | |
|-------|--------|
| 0° | 9141.9 |
| 2.5° | 9398.9 |
| 5° | 9331.0 |
| 7.5° | 9352.5 |
| 10° | 9335.8 |
| 12.5° | 9143.1 |
| 15° | 8723.1 |
| 17.5° | 8159.2 |
| 20° | 7482.2 |
| 22.5° | 6757.7 |
| 25° | 5836.8 |
| 27.5° | 4668.5 |
| 30° | 3772.6 |
| 32.5° | 2907.7 |
| 35° | 1788.2 |
| 37.5° | 765.0 |
| 40° | 271.3 |
| 42.5° | 249.8 |
| 45° | 245.1 |
| 47.5° | 236.8 |
| 50° | 227.2 |
| 52.5° | 216.5 |
| 55° | 205.8 |
| 57.5° | 195.1 |
| 60° | 184.4 |
| 62.5° | 172.5 |
| 65° | 159.4 |
| 67.5° | 146.3 |
| 70° | 132.1 |
| 72.5° | 116.6 |
| 75° | 101.1 |
| 77.5° | 83.3 |
| 80° | 65.4 |
| 82.5° | 46.4 |
| 85° | 27.4 |
| 87.5° | 9.5 |
| 90° | 0.0 |

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)