

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P771605

Luminaire Tested: LD6D75BD010-EU6DR6570959024-6LBS1MW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P771605
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D75BD010-EU6DR6570959024-6LBS1MW
Description: 6 INCH ROUND SHALLOW MATTE WHITE TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6407.2 lumens
Efficiency: N/A
Efficacy: 88.5 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct


Input Watts (W): 72.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P771605
CATALOG NUMBER: LD6D75BD010-EU6DR6570959024-6LBS1MW

Luminous Intensity Polar Plot





TEST NUMBER: P771605

CATALOG NUMBER: LD6D75BD010-EU6DR6570959024-6LBS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93																			
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85																			
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78																			
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72																			
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66																			
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61																			
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56																			
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52																			
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49																			
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	339765
5°	338911
10°	338619
15°	328181
20°	298771
25°	260357
30°	216547
35°	171579
40°	123838
45°	78235
50°	40778
55°	21678
60°	11389
65°	6260
70°	2630
75°	2888
80°	2018
85°	1742

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 78235 cd/sqm



TEST NUMBER: P771605

CATALOG NUMBER: LD6D75BD010-EU6DR6570959024-6LBS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	550.2	8.6
10°-20°	1506.5	23.5
20°-30°	1841.5	28.7
30°-40°	1494.1	23.3
40°-50°	744.5	11.6
50°-60°	207.7	3.2
60°-70°	47.2	0.7
70°-80°	12.3	0.2
80°-90°	3.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3898.2	60.8
0°-40°	5392.3	84.2
0°-60°	6344.6	99.0
0°-90°	6407.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6407.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5818	
5°	5781	550
15°	5428	1507
25°	4040	1842
35°	2406	1494
45°	947	745
55°	213	208
65°	45	47
75°	13	12
85°	3	3
90°	0	



TEST NUMBER: P771605

CATALOG NUMBER: LD6D75BD010-EU6DR6570959024-6LBS1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	5817.5
2.5°	5813.3
5°	5780.8
7.5°	5762.0
10°	5709.8
12.5°	5603.8
15°	5427.7
17.5°	5152.4
20°	4807.1
22.5°	4434.3
25°	4040.2
27.5°	3618.8
30°	3211.0
32.5°	2808.3
35°	2406.5
37.5°	2005.6
40°	1624.3
42.5°	1266.9
45°	947.2
47.5°	660.0
50°	448.8
52.5°	309.5
55°	212.9
57.5°	143.6
60°	97.5
62.5°	67.5
65°	45.3
67.5°	23.1
70°	15.4
72.5°	14.5
75°	12.8
77.5°	8.5
80°	6.0
82.5°	4.3
85°	2.6
87.5°	1.7
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)