

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P771678

Luminaire Tested: LD6D75BD010-EU6DR7070959024-6LBDP1LI

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P771678
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D75BD010-EU6DR7070959024-6LBDP1LI
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7748.1 lumens
Efficiency: N/A
Efficacy: 107.0 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 72.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P771678

CATALOG NUMBER: LD6D75BD010-EU6DR7070959024-6LBDP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P771678
 CATALOG NUMBER: LD6D75BD010-EU6DR7070959024-6LBDP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	951781
5°	923501
10°	897755
15°	885974
20°	827316
25°	621526
30°	439364
35°	155631
40°	81841
45°	87164
50°	90259
55°	91950
60°	92522
65°	90564
70°	85487
75°	79196
80°	70282
85°	57040

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 92545 cd/sqm



TEST NUMBER: P771678

CATALOG NUMBER: LD6D75BD010-EU6DR7070959024-6LBDP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	794.2	10.3
10°-20°	2178.4	28.1
20°-30°	2399.2	31.0
30°-40°	916.7	11.8
40°-50°	432.8	5.6
50°-60°	430.3	5.6
60°-70°	344.5	4.4
70°-80°	198.0	2.6
80°-90°	53.8	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5371.9	69.3
0°-40°	6288.6	81.2
0°-60°	7151.7	92.3
0°-90°	7748.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7748.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8711	
5°	8420	794
15°	7832	2178
25°	5156	2399
35°	1167	917
45°	564	433
55°	483	430
65°	350	345
75°	188	198
85°	46	54
90°	0	



TEST NUMBER: P771678

CATALOG NUMBER: LD6D75BD010-EU6DR7070959024-6LBDP1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	8711.1
2.5°	8620.1
5°	8420.1
7.5°	8253.2
10°	8091.8
12.5°	7955.3
15°	7832.5
17.5°	7536.0
20°	7115.3
22.5°	6207.8
25°	5155.5
27.5°	4487.9
30°	3482.5
32.5°	2249.5
35°	1166.8
37.5°	630.3
40°	573.8
42.5°	569.6
45°	564.1
47.5°	551.7
50°	531.0
52.5°	507.5
55°	482.7
57.5°	455.1
60°	423.4
62.5°	387.6
65°	350.3
67.5°	308.9
70°	267.6
72.5°	226.2
75°	187.6
77.5°	147.6
80°	111.7
82.5°	78.6
85°	45.5
87.5°	17.9
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)