

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P769272

Luminaire Tested: LD6D60D010-EU6DR6555659027-6LBDP1H

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P769272
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D60D010-EU6DR6555659027-6LBDP1H
Description: 6 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6089.8 lumens
Efficiency: N/A
Efficacy: 94.6 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 64.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P769272
CATALOG NUMBER: LD6D60D010-EU6DR6555659027-6LBDP1H

Luminous Intensity Polar Plot





TEST NUMBER: P769272

CATALOG NUMBER: LD6D60D010-EU6DR6555659027-6LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93		
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87		
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80		
4	97	89	84	79	95	88	83	79	86	82	78	84	80	77	82	79	76	75		
5	92	83	78	73	90	83	77	73	81	76	72	79	75	72	77	74	71	69		
6	87	78	72	68	86	77	72	68	76	71	67	74	70	67	73	69	66	65		
7	83	73	67	63	81	73	67	63	71	66	62	70	66	62	69	65	62	60		
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	57		
9	75	65	59	55	74	65	59	55	64	58	55	63	58	55	62	58	54	53		
10	71	61	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	655106
5°	655645
10°	678736
15°	679855
20°	625920
25°	533315
30°	408278
35°	288440
40°	170257
45°	69116
50°	25055
55°	13963
60°	7998
65°	4395
70°	4632
75°	3588
80°	3775
85°	3259

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 69116 cd/sqm



TEST NUMBER: P769272

CATALOG NUMBER: LD6D60D010-EU6DR6555659027-6LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	577.3	9.5
10°-20°	1665.4	27.3
20°-30°	1998.1	32.8
30°-40°	1342.8	22.1
40°-50°	402.0	6.6
50°-60°	70.9	1.2
60°-70°	20.2	0.3
70°-80°	9.9	0.2
80°-90°	3.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4240.9	69.6
0°-40°	5583.7	91.7
0°-60°	6056.6	99.5
0°-90°	6089.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6089.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5996	
5°	5978	577
15°	6010	1665
25°	4424	1998
35°	2162	1343
45°	447	402
55°	73	71
65°	17	20
75°	8	10
85°	3	3
90°	0	



TEST NUMBER: P769272
CATALOG NUMBER: LD6D60D010-EU6DR6555659027-6LBDP1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	5995.8
2.5°	6021.4
5°	5977.9
7.5°	6068.3
10°	6117.7
12.5°	6105.7
15°	6010.3
17.5°	5776.9
20°	5383.2
22.5°	4919.7
25°	4423.8
27.5°	3864.0
30°	3236.1
32.5°	2666.9
35°	2162.5
37.5°	1664.0
40°	1193.7
42.5°	779.6
45°	447.3
47.5°	236.9
50°	147.4
52.5°	102.2
55°	73.3
57.5°	52.8
60°	36.6
62.5°	23.9
65°	17.0
67.5°	15.3
70°	14.5
72.5°	11.1
75°	8.5
77.5°	7.7
80°	6.0
82.5°	4.3
85°	2.6
87.5°	1.7
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)