

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P769365

Luminaire Tested: LD6D60D010-EU6DR7055659030-6LBDP1MW

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P769365
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D60D010-EU6DR7055659030-6LBDP1MW
Description: 6 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5645.2 lumens
Efficiency: N/A
Efficacy: 87.7 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 64.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P769365

CATALOG NUMBER: LD6D60D010-EU6DR7055659030-6LBDP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P769365

CATALOG NUMBER: LD6D60D010-EU6DR7055659030-6LBDP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91		
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83		
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76		
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70		
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65		
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61		
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57		
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53		
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50		
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	693456
5°	672853
10°	654095
15°	645514
20°	602782
25°	452832
30°	320115
35°	113389
40°	59619
45°	63507
50°	65765
55°	66995
60°	67414
65°	65978
70°	62262
75°	57708
80°	51217
85°	41620

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 67431 cd/sqm



TEST NUMBER: P769365

CATALOG NUMBER: LD6D60D010-EU6DR7055659030-6LBDP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	578.6	10.3
10°-20°	1587.2	28.1
20°-30°	1748.1	31.0
30°-40°	667.9	11.8
40°-50°	315.4	5.6
50°-60°	313.5	5.6
60°-70°	251.0	4.4
70°-80°	144.3	2.6
80°-90°	39.2	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3913.9	69.3
0°-40°	4581.8	81.2
0°-60°	5210.7	92.3
0°-90°	5645.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5645.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6347	
5°	6135	579
15°	5707	1587
25°	3756	1748
35°	850	668
45°	411	315
55°	352	314
65°	255	251
75°	137	144
85°	33	39
90°	0	



TEST NUMBER: P769365

CATALOG NUMBER: LD6D60D010-EU6DR7055659030-6LBDP1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	6346.8
2.5°	6280.5
5°	6134.8
7.5°	6013.2
10°	5895.6
12.5°	5796.1
15°	5706.7
17.5°	5490.6
20°	5184.2
22.5°	4522.9
25°	3756.2
27.5°	3269.9
30°	2537.3
32.5°	1639.0
35°	850.1
37.5°	459.2
40°	418.0
42.5°	415.0
45°	411.0
47.5°	402.0
50°	386.9
52.5°	369.8
55°	351.7
57.5°	331.6
60°	308.5
62.5°	282.4
65°	255.2
67.5°	225.1
70°	194.9
72.5°	164.8
75°	136.7
77.5°	107.5
80°	81.4
82.5°	57.3
85°	33.2
87.5°	13.1
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)