

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P771546

Luminaire Tested: LD6D75BD010-EU6DR6070959030-6LBDP1B

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P771546  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD6D75BD010-EU6DR6070959030-6LBDP1B  
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 60° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6737.2 lumens  
Efficiency: N/A  
Efficacy: 93.1 lumens/watt  
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct


Input Watts (W): 72.4  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



Downlight

TEST NUMBER: P771546  
CATALOG NUMBER: LD6D75BD010-EU6DR6070959030-6LBDP1B

### Luminous Intensity Polar Plot





TEST NUMBER: P771546

CATALOG NUMBER: LD6D75BD010-EU6DR6070959030-6LBDP1B

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93																			
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86																			
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80																			
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70																			
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66																			
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62																			
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59																			
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55																			
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	874228
5°	895719
10°	906542
15°	863600
20°	761436
25°	615872
30°	416579
35°	208757
40°	33860
45°	33144
50°	33809
55°	34307
60°	35269
65°	36065
70°	36929
75°	37360
80°	36054
85°	29962

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 75°  
 Luminance: 37360 cd/sqm



TEST NUMBER: P771546

CATALOG NUMBER: LD6D75BD010-EU6DR6070959030-6LBDP1B

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	780.5	11.6
10°-20°	2111.8	31.3
20°-30°	2272.1	33.7
30°-40°	987.6	14.7
40°-50°	165.9	2.5
50°-60°	161.3	2.4
60°-70°	138.0	2.0
70°-80°	92.3	1.4
80°-90°	27.6	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5164.5	76.7
0°-40°	6152.1	91.3
0°-60°	6479.3	96.2
0°-90°	6737.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6737.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	8001	
5°	8167	781
15°	7635	2112
25°	5109	2272
35°	1565	988
45°	214	166
55°	180	161
65°	140	138
75°	88	92
85°	24	28
90°	0	



TEST NUMBER: P771546

CATALOG NUMBER: LD6D75BD010-EU6DR6070959030-6LBDP1B

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	8001.3
2.5°	8226.2
5°	8166.8
7.5°	8185.6
10°	8171.0
12.5°	8002.3
15°	7634.7
17.5°	7141.2
20°	6548.7
22.5°	5914.5
25°	5108.6
27.5°	4086.0
30°	3301.9
32.5°	2544.9
35°	1565.1
37.5°	669.5
40°	237.4
42.5°	218.7
45°	214.5
47.5°	207.2
50°	198.9
52.5°	189.5
55°	180.1
57.5°	170.8
60°	161.4
62.5°	151.0
65°	139.5
67.5°	128.1
70°	115.6
72.5°	102.0
75°	88.5
77.5°	72.9
80°	57.3
82.5°	40.6
85°	23.9
87.5°	8.3
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)