

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P771702

Luminaire Tested: LD6D75BD010-EU6DR7070959030-6LBDP1B

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P771702  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD6D75BD010-EU6DR7070959030-6LBDP1B  
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 70° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5010.4 lumens  
Efficiency: N/A  
Efficacy: 69.2 lumens/watt  
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct


Input Watts (W): 72.4  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



Downlight

TEST NUMBER: P771702  
CATALOG NUMBER: LD6D75BD010-EU6DR7070959030-6LBDP1B

### Luminous Intensity Polar Plot





TEST NUMBER: P771702

CATALOG NUMBER: LD6D75BD010-EU6DR7070959030-6LBDP1B

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	615477
5°	597186
10°	580549
15°	572928
20°	534995
25°	401909
30°	284120
35°	100637
40°	52916
45°	56368
50°	58371
55°	59471
60°	59831
65°	58558
70°	55266
75°	51207
80°	45429
85°	36857

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 57.5°  
 Luminance: 59846 cd/sqm



TEST NUMBER: P771702

CATALOG NUMBER: LD6D75BD010-EU6DR7070959030-6LBDP1B

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	513.6	10.3
10°-20°	1408.7	28.1
20°-30°	1551.5	31.0
30°-40°	592.8	11.8
40°-50°	279.9	5.6
50°-60°	278.3	5.6
60°-70°	222.8	4.4
70°-80°	128.0	2.6
80°-90°	34.8	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3473.8	69.3
0°-40°	4066.6	81.2
0°-60°	4624.7	92.3
0°-90°	5010.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5010.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	5633	
5°	5445	514
15°	5065	1409
25°	3334	1552
35°	754	593
45°	365	280
55°	312	278
65°	226	223
75°	121	128
85°	29	35
90°	0	



TEST NUMBER: P771702

CATALOG NUMBER: LD6D75BD010-EU6DR7070959030-6LBDP1B

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	5633.1
2.5°	5574.2
5°	5444.9
7.5°	5337.0
10°	5232.7
12.5°	5144.4
15°	5065.0
17.5°	4873.2
20°	4601.2
22.5°	4014.4
25°	3333.8
27.5°	2902.2
30°	2252.0
32.5°	1454.7
35°	754.5
37.5°	407.6
40°	371.0
42.5°	368.3
45°	364.8
47.5°	356.8
50°	343.4
52.5°	328.2
55°	312.2
57.5°	294.3
60°	273.8
62.5°	250.6
65°	226.5
67.5°	199.8
70°	173.0
72.5°	146.3
75°	121.3
77.5°	95.4
80°	72.2
82.5°	50.8
85°	29.4
87.5°	11.6
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)