

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P768923

Luminaire Tested: LD6D60D010-EU6DR4055659040-6LBDP1MW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P768923
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-28)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D60D010-EU6DR4055659040-6LBDP1MW
Description: 6 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 40° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7501.1 lumens
Efficiency: N/A
Efficacy: 116.5 lumens/watt
Spacing Criteria (0/90/45): 0.68 / 0.68 / 0.6
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 64.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P768923

CATALOG NUMBER: LD6D60D010-EU6DR4055659040-6LBDP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P768923

CATALOG NUMBER: LD6D60D010-EU6DR4055659040-6LBDP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20																	
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR																																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100									100																		
1	115	112	110	108	112	110	108	107	106	105	103	103	101	100	99	98	97	96									96																		
2	110	106	103	100	108	105	102	99	102	99	97	99	97	95	96	95	93	92									92																		
3	106	101	97	94	104	100	96	93	97	94	92	95	93	90	93	91	89	88									88																		
4	102	97	92	89	101	95	91	88	93	90	87	92	89	86	90	87	85	84									84																		
5	99	92	88	84	97	91	87	84	90	86	83	88	85	83	87	84	82	81									81																		
6	95	88	84	80	94	88	83	80	86	82	80	85	82	79	84	81	79	77									77																		
7	92	85	80	77	91	84	80	77	83	79	76	82	79	76	81	78	76	74									74																		
8	89	82	77	74	88	81	77	74	80	76	73	79	76	73	78	75	73	72									72																		
9	86	79	74	71	85	78	74	71	77	73	71	76	73	70	76	72	70	69									69																		
10	83	76	71	68	82	75	71	68	75	71	68	74	70	68	73	70	68	67									67																		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1908195
5°	1898923
10°	1794889
15°	1525888
20°	1040003
25°	433929
30°	136446
35°	63410
40°	35073
45°	16085
50°	7802
55°	4267
60°	2229
65°	801
70°	319
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 16085 cd/sqm



TEST NUMBER: P768923

CATALOG NUMBER: LD6D60D010-EU6DR4055659040-6LBDP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1616.6	21.6
10°-20°	3621.7	48.3
20°-30°	1812.9	24.2
30°-40°	332.3	4.4
40°-50°	91.7	1.2
50°-60°	21.5	0.3
60°-70°	4.1	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	7051.3	94.0
0°-40°	7383.6	98.4
0°-60°	7496.8	99.9
0°-90°	7501.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7501.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	17465	
5°	17314	###
15°	13490	3622
25°	3599	1813
35°	475	332
45°	104	92
55°	22	22
65°	3	4
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P768923

CATALOG NUMBER: LD6D60D010-EU6DR4055659040-6LBDP1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	17464.6
2.5°	17439.0
5°	17313.6
7.5°	16913.6
10°	16178.0
12.5°	15031.3
15°	13489.7
17.5°	11484.9
20°	8944.5
22.5°	6098.0
25°	3599.4
27.5°	1902.8
30°	1081.5
32.5°	698.9
35°	475.4
37.5°	339.7
40°	245.9
42.5°	168.3
45°	104.1
47.5°	66.3
50°	45.9
52.5°	32.6
55°	22.4
57.5°	14.3
60°	10.2
62.5°	6.1
65°	3.1
67.5°	2.0
70°	1.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)