

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P768927

Luminaire Tested: LD6D60D010-EU6DR4055659040-6LBS1MW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P768927
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-28)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D60D010-EU6DR4055659040-6LBS1MW
Description: 6 INCH ROUND SHALLOW MATTE WHITE TRIM, WITH 40° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7906.2 lumens
Efficiency: N/A
Efficacy: 122.8 lumens/watt
Spacing Criteria (0/90/45): 0.68 / 0.68 / 0.6
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 64.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P768927
CATALOG NUMBER: LD6D60D010-EU6DR4055659040-6LBS1MW

Luminous Intensity Polar Plot





TEST NUMBER: P768927

CATALOG NUMBER: LD6D60D010-EU6DR4055659040-6LBS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
|-----|----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|--|--|--|--|--|--|----|--|--|--|--|--|--|--|--|
| RF | 20 | | | | | | | | | 20 | | | | | | | | | 20 | | | | | | | | | 20 | | | | | | | | | 20 | | | | | | | | |
| RC | 80 | | | | | | | | | 50 | | | | | | | | | 30 | | | | | | | | | 10 | | | | | | | | | 0 | | | | | | | | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 | | | | | | | | | | | | | | | |
| RCR | 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | 100 | 100 | 100 | 100 | 100 | 100 | 100 | 100 | 100 | 100 | | | | | | | | | | | | | | | | |
| | 1 | 115 | 112 | 110 | 108 | 112 | 110 | 108 | 107 | 106 | 105 | 103 | 103 | 101 | 100 | 99 | 98 | 97 | 96 | 96 | 96 | 96 | 96 | 96 | 96 | 96 | 96 | 96 | 96 | 96 | | | | | | | | | | | | | | | |
| | 2 | 110 | 106 | 103 | 100 | 108 | 105 | 102 | 99 | 102 | 99 | 97 | 99 | 97 | 95 | 96 | 95 | 93 | 92 | 92 | 92 | 92 | 92 | 92 | 92 | 92 | 92 | 92 | 92 | 92 | | | | | | | | | | | | | | | |
| | 3 | 106 | 101 | 97 | 94 | 104 | 100 | 96 | 93 | 97 | 94 | 92 | 95 | 93 | 90 | 93 | 91 | 89 | 88 | 88 | 88 | 88 | 88 | 88 | 88 | 88 | 88 | 88 | 88 | 88 | | | | | | | | | | | | | | | |
| | 4 | 102 | 97 | 92 | 89 | 101 | 95 | 91 | 88 | 93 | 90 | 87 | 92 | 89 | 86 | 90 | 87 | 85 | 84 | 84 | 84 | 84 | 84 | 84 | 84 | 84 | 84 | 84 | 84 | 84 | | | | | | | | | | | | | | | |
| | 5 | 99 | 92 | 88 | 84 | 97 | 91 | 87 | 84 | 90 | 86 | 83 | 88 | 85 | 83 | 87 | 84 | 82 | 81 | 81 | 81 | 81 | 81 | 81 | 81 | 81 | 81 | 81 | 81 | 81 | | | | | | | | | | | | | | | |
| | 6 | 95 | 88 | 84 | 80 | 94 | 88 | 83 | 80 | 86 | 82 | 80 | 85 | 82 | 79 | 84 | 81 | 79 | 77 | 77 | 77 | 77 | 77 | 77 | 77 | 77 | 77 | 77 | 77 | 77 | | | | | | | | | | | | | | | |
| | 7 | 92 | 85 | 80 | 77 | 91 | 84 | 80 | 77 | 83 | 79 | 76 | 82 | 79 | 76 | 81 | 78 | 76 | 74 | 74 | 74 | 74 | 74 | 74 | 74 | 74 | 74 | 74 | 74 | 74 | | | | | | | | | | | | | | | |
| | 8 | 89 | 82 | 77 | 74 | 88 | 81 | 77 | 74 | 80 | 76 | 73 | 79 | 76 | 73 | 78 | 75 | 73 | 72 | 72 | 72 | 72 | 72 | 72 | 72 | 72 | 72 | 72 | 72 | 72 | | | | | | | | | | | | | | | |
| | 9 | 86 | 79 | 74 | 71 | 85 | 78 | 74 | 71 | 77 | 73 | 71 | 76 | 73 | 70 | 76 | 72 | 70 | 69 | 69 | 69 | 69 | 69 | 69 | 69 | 69 | 69 | 69 | 69 | 69 | | | | | | | | | | | | | | | |
| | 10 | 83 | 76 | 71 | 68 | 82 | 75 | 71 | 68 | 75 | 71 | 68 | 74 | 70 | 68 | 73 | 70 | 68 | 67 | 67 | 67 | 67 | 67 | 67 | 67 | 67 | 67 | 67 | 67 | 67 | | | | | | | | | | | | | | | |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|---------|
| | 0° |
| 0° | 2011228 |
| 5° | 2001450 |
| 10° | 1891812 |
| 15° | 1608281 |
| 20° | 1096162 |
| 25° | 457365 |
| 30° | 143814 |
| 35° | 66838 |
| 40° | 36970 |
| 45° | 16951 |
| 50° | 8227 |
| 55° | 4515 |
| 60° | 2360 |
| 65° | 827 |
| 70° | 351 |
| 75° | 0 |
| 80° | 0 |
| 85° | 0 |

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 16951 cd/sqm



TEST NUMBER: P768927

CATALOG NUMBER: LD6D60D010-EU6DR4055659040-6LBS1MW

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 1703.9 | 21.6 |
| 10°-20° | 3817.3 | 48.3 |
| 20°-30° | 1910.8 | 24.2 |
| 30°-40° | 350.3 | 4.4 |
| 40°-50° | 96.6 | 1.2 |
| 50°-60° | 22.7 | 0.3 |
| 60°-70° | 4.4 | 0.1 |
| 70°-80° | 0.1 | 0.0 |
| 80°-90° | 0.0 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 7432.0 | 94.0 |
| 0°-40° | 7782.3 | 98.4 |
| 0°-60° | 7901.7 | 99.9 |
| 0°-90° | 7906.2 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 7906.2 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|-------|------|
| 0° | 18408 | |
| 5° | 18248 | ### |
| 15° | 14218 | 3817 |
| 25° | 3794 | 1911 |
| 35° | 501 | 350 |
| 45° | 110 | 97 |
| 55° | 24 | 23 |
| 65° | 3 | 4 |
| 75° | 0 | 0 |
| 85° | 0 | 0 |
| 90° | 0 | |



TEST NUMBER: P768927

CATALOG NUMBER: LD6D60D010-EU6DR4055659040-6LBS1MW

CANDELA DISTRIBUTION (FULL):

| 0° | |
|-------|---------|
| 0° | 18407.6 |
| 2.5° | 18380.7 |
| 5° | 18248.4 |
| 7.5° | 17826.9 |
| 10° | 17051.6 |
| 12.5° | 15842.9 |
| 15° | 14218.1 |
| 17.5° | 12105.0 |
| 20° | 9427.5 |
| 22.5° | 6427.3 |
| 25° | 3793.8 |
| 27.5° | 2005.5 |
| 30° | 1139.9 |
| 32.5° | 736.6 |
| 35° | 501.1 |
| 37.5° | 358.1 |
| 40° | 259.2 |
| 42.5° | 177.4 |
| 45° | 109.7 |
| 47.5° | 69.9 |
| 50° | 48.4 |
| 52.5° | 34.4 |
| 55° | 23.7 |
| 57.5° | 15.1 |
| 60° | 10.8 |
| 62.5° | 6.5 |
| 65° | 3.2 |
| 67.5° | 2.2 |
| 70° | 1.1 |
| 72.5° | 0.0 |
| 75° | 0.0 |
| 77.5° | 0.0 |
| 80° | 0.0 |
| 82.5° | 0.0 |
| 85° | 0.0 |
| 87.5° | 0.0 |
| 90° | 0.0 |

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)