

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P771716

Luminaire Tested: LD6D75BD010-EU6DR7070959035-6LBDP1H

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P771716  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD6D75BD010-EU6DR7070959035-6LBDP1H  
Description: 6 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 70° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 8702.3 lumens  
Efficiency: N/A  
Efficacy: 120.2 lumens/watt  
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct


Input Watts (W): 72.4  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



Downlight

TEST NUMBER: P771716  
CATALOG NUMBER: LD6D75BD010-EU6DR7070959035-6LBDP1H

### Luminous Intensity Polar Plot





TEST NUMBER: P771716  
 CATALOG NUMBER: LD6D75BD010-EU6DR7070959035-6LBDP1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1068985
5°	1037226
10°	1008313
15°	995084
20°	929206
25°	698067
30°	493476
35°	174798
40°	91911
45°	97903
50°	101376
55°	103284
60°	103929
65°	101733
70°	95997
75°	88947
80°	78966
85°	64060

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 57.5°  
 Luminance: 103953 cd/sqm



TEST NUMBER: P771716

CATALOG NUMBER: LD6D75BD010-EU6DR7070959035-6LBDP1H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	892.0	10.3
10°-20°	2446.7	28.1
20°-30°	2694.7	31.0
30°-40°	1029.6	11.8
40°-50°	486.2	5.6
50°-60°	483.3	5.6
60°-70°	387.0	4.4
70°-80°	222.4	2.6
80°-90°	60.5	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6033.4	69.3
0°-40°	7063.0	81.2
0°-60°	8032.5	92.3
0°-90°	8702.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8702.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	9784	
5°	9457	892
15°	8797	2447
25°	5790	2695
35°	1310	1030
45°	634	486
55°	542	483
65°	394	387
75°	211	222
85°	51	60
90°	0	



TEST NUMBER: P771716

CATALOG NUMBER: LD6D75BD010-EU6DR7070959035-6LBDP1H

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	9783.8
2.5°	9681.6
5°	9457.0
7.5°	9269.5
10°	9088.3
12.5°	8934.9
15°	8797.1
17.5°	8464.0
20°	7991.6
22.5°	6972.3
25°	5790.4
27.5°	5040.6
30°	3911.4
32.5°	2526.5
35°	1310.5
37.5°	707.9
40°	644.4
42.5°	639.8
45°	633.6
47.5°	619.6
50°	596.4
52.5°	570.1
55°	542.2
57.5°	511.2
60°	475.6
62.5°	435.3
65°	393.5
67.5°	347.0
70°	300.5
72.5°	254.0
75°	210.7
77.5°	165.7
80°	125.5
82.5°	88.3
85°	51.1
87.5°	20.1
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)