

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P769963

Luminaire Tested: LD6D65D010-EU6DR6055659024-6LBDP1MW

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P769963
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D65D010-EU6DR6055659024-6LBDP1MW
Description: 6 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6162.4 lumens
Efficiency: N/A
Efficacy: 84.6 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 72.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P769963

CATALOG NUMBER: LD6D65D010-EU6DR6055659024-6LBDP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P769963

CATALOG NUMBER: LD6D65D010-EU6DR6055659024-6LBDP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93																			
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86																			
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80																			
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70																			
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66																			
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62																			
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59																			
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55																			
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	799636
5°	819306
10°	829201
15°	789928
20°	696474
25°	563322
30°	381039
35°	190937
40°	30979
45°	30316
50°	30919
55°	31393
60°	32254
65°	32989
70°	33767
75°	34194
80°	32970
85°	27454

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 75°
 Luminance: 34194 cd/sqm



TEST NUMBER: P769963

CATALOG NUMBER: LD6D65D010-EU6DR6055659024-6LBDP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	714.0	11.6
10°-20°	1931.6	31.3
20°-30°	2078.3	33.7
30°-40°	903.4	14.7
40°-50°	151.7	2.5
50°-60°	147.5	2.4
60°-70°	126.2	2.0
70°-80°	84.4	1.4
80°-90°	25.2	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4723.9	76.7
0°-40°	5627.3	91.3
0°-60°	5926.5	96.2
0°-90°	6162.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6162.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7319	
5°	7470	714
15°	6983	1932
25°	4673	2078
35°	1432	903
45°	196	152
55°	165	148
65°	128	126
75°	81	84
85°	22	25
90°	0	



TEST NUMBER: P769963

CATALOG NUMBER: LD6D65D010-EU6DR6055659024-6LBDP1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	7318.6
2.5°	7524.4
5°	7470.1
7.5°	7487.2
10°	7473.9
12.5°	7319.6
15°	6983.4
17.5°	6531.9
20°	5990.0
22.5°	5409.9
25°	4672.7
27.5°	3737.4
30°	3020.2
32.5°	2327.8
35°	1431.5
37.5°	612.4
40°	217.2
42.5°	200.0
45°	196.2
47.5°	189.5
50°	181.9
52.5°	173.3
55°	164.8
57.5°	156.2
60°	147.6
62.5°	138.1
65°	127.6
67.5°	117.2
70°	105.7
72.5°	93.3
75°	81.0
77.5°	66.7
80°	52.4
82.5°	37.1
85°	21.9
87.5°	7.6
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)