

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P771273

Luminaire Tested: LD6D75BD010-EU6DR4070959050-6LBDP1B

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P771273  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-28)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD6D75BD010-EU6DR4070959050-6LBDP1B  
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 40° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 8455.7 lumens  
Efficiency: N/A  
Efficacy: 116.8 lumens/watt  
Spacing Criteria (0/90/45): 0.68 / 0.68 / 0.6  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 72.4  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



Downlight

TEST NUMBER: P771273  
CATALOG NUMBER: LD6D75BD010-EU6DR4070959050-6LBDP1B

### Luminous Intensity Polar Plot





TEST NUMBER: P771273  
 CATALOG NUMBER: LD6D75BD010-EU6DR4070959050-6LBDP1B

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				
1	115	112	110	108	112	110	108	107	106	105	103	103	101	100	99	98	97	96				
2	110	106	103	100	108	105	102	99	102	99	97	99	97	95	96	95	93	92				
3	106	101	97	94	104	100	96	93	97	94	92	95	93	90	93	91	89	88				
4	102	97	92	89	101	95	91	88	93	90	87	92	89	86	90	87	85	84				
5	99	92	88	84	97	91	87	84	90	86	83	88	85	83	87	84	82	81				
6	95	88	84	80	94	88	83	80	86	82	80	85	82	79	84	81	79	77				
7	92	85	80	77	91	84	80	77	83	79	76	82	79	76	81	78	76	74				
8	89	82	77	74	88	81	77	74	80	76	73	79	76	73	78	75	73	72				
9	86	79	74	71	85	78	74	71	77	73	71	76	73	70	76	72	70	69				
10	83	76	71	68	82	75	71	68	75	71	68	74	70	68	73	70	68	67				

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	2151016
5°	2140566
10°	2023294
15°	1720061
20°	1172344
25°	489156
30°	153806
35°	71480
40°	39537
45°	18125
50°	8805
55°	4819
60°	2513
65°	905
70°	383
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 18125 cd/sqm



TEST NUMBER: P771273

CATALOG NUMBER: LD6D75BD010-EU6DR4070959050-6LBDP1B

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	1822.4	21.6
10°-20°	4082.6	48.3
20°-30°	2043.6	24.2
30°-40°	374.6	4.4
40°-50°	103.4	1.2
50°-60°	24.3	0.3
60°-70°	4.7	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	7948.6	94.0
0°-40°	8323.2	98.4
0°-60°	8450.9	99.9
0°-90°	8455.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8455.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	19687	
5°	19517	###
15°	15206	4083
25°	4058	2044
35°	536	375
45°	117	103
55°	25	24
65°	4	5
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P771273

CATALOG NUMBER: LD6D75BD010-EU6DR4070959050-6LBDP1B

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	19687.0
2.5°	19658.2
5°	19516.8
7.5°	19065.9
10°	18236.7
12.5°	16944.0
15°	15206.3
17.5°	12946.4
20°	10082.7
22.5°	6874.0
25°	4057.5
27.5°	2144.9
30°	1219.1
32.5°	787.8
35°	535.9
37.5°	383.0
40°	277.2
42.5°	189.8
45°	117.3
47.5°	74.8
50°	51.8
52.5°	36.8
55°	25.3
57.5°	16.1
60°	11.5
62.5°	6.9
65°	3.5
67.5°	2.3
70°	1.2
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)