

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P771585

Luminaire Tested: LD6D75BD010-EU6DR6070959050-6LBDP1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P771585
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D75BD010-EU6DR6070959050-6LBDP1B
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7177.3 lumens
Efficiency: N/A
Efficacy: 99.1 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 72.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P771585
CATALOG NUMBER: LD6D75BD010-EU6DR6070959050-6LBDP1B

Luminous Intensity Polar Plot





TEST NUMBER: P771585

CATALOG NUMBER: LD6D75BD010-EU6DR6070959050-6LBDP1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93	93	93	93
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86	86	86	86
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80	80	80	80
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75	75	75	75
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70	70	70	70
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66	66	66	66
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62	62	62	62
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59	59	59	59
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55	55	55	55
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53	53	53	53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	931339
5°	954243
10°	965765
15°	920021
20°	811178
25°	656101
30°	443805
35°	222389
40°	36071
45°	35307
50°	36019
55°	36555
60°	37564
65°	38418
70°	39325
75°	39809
80°	38382
85°	31967

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 75°
 Luminance: 39809 cd/sqm



TEST NUMBER: P771585

CATALOG NUMBER: LD6D75BD010-EU6DR6070959050-6LBDP1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	831.5	11.6
10°-20°	2249.8	31.3
20°-30°	2420.6	33.7
30°-40°	1052.2	14.7
40°-50°	176.7	2.5
50°-60°	171.8	2.4
60°-70°	146.9	2.0
70°-80°	98.3	1.4
80°-90°	29.4	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5501.9	76.7
0°-40°	6554.1	91.3
0°-60°	6902.6	96.2
0°-90°	7177.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7177.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8524	
5°	8700	832
15°	8134	2250
25°	5442	2421
35°	1667	1052
45°	228	177
55°	192	172
65°	149	147
75°	94	98
85°	26	29
90°	0	



TEST NUMBER: P771585

CATALOG NUMBER: LD6D75BD010-EU6DR6070959050-6LBDP1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	8524.0
2.5°	8763.6
5°	8700.4
7.5°	8720.4
10°	8704.8
12.5°	8525.1
15°	8133.5
17.5°	7607.7
20°	6976.5
22.5°	6300.9
25°	5442.3
27.5°	4353.0
30°	3517.7
32.5°	2711.2
35°	1667.3
37.5°	713.3
40°	252.9
42.5°	233.0
45°	228.5
47.5°	220.8
50°	211.9
52.5°	201.9
55°	191.9
57.5°	181.9
60°	171.9
62.5°	160.9
65°	148.6
67.5°	136.4
70°	123.1
72.5°	108.7
75°	94.3
77.5°	77.7
80°	61.0
82.5°	43.3
85°	25.5
87.5°	8.9
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)