

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P769679

Luminaire Tested: LD6D65D010-EU6DR4055659030-6LBS1H

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P769679
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-28)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D65D010-EU6DR4055659030-6LBS1H
Description: 6 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 40° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8701.7 lumens
Efficiency: N/A
Efficacy: 119.5 lumens/watt
Spacing Criteria (0/90/45): 0.68 / 0.68 / 0.6
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 72.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P769679
CATALOG NUMBER: LD6D65D010-EU6DR4055659030-6LBS1H

Luminous Intensity Polar Plot





TEST NUMBER: P769679

CATALOG NUMBER: LD6D65D010-EU6DR4055659030-6LBS1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						100													
1	115	112	110	108	112	110	108	107	106	105	103	103	101	100	99	98	97	96						96													
2	110	106	103	100	108	105	102	99	102	99	97	99	97	95	96	95	93	92						92													
3	106	101	97	94	104	100	96	93	97	94	92	95	93	90	93	91	89	88						88													
4	102	97	92	89	101	95	91	88	93	90	87	92	89	86	90	87	85	84						84													
5	99	92	88	84	97	91	87	84	90	86	83	88	85	83	87	84	82	81						81													
6	95	88	84	80	94	88	83	80	86	82	80	85	82	79	84	81	79	77						77													
7	92	85	80	77	91	84	80	77	83	79	76	82	79	76	81	78	76	74						74													
8	89	82	77	74	88	81	77	74	80	76	73	79	76	73	78	75	73	72						72													
9	86	79	74	71	85	78	74	71	77	73	71	76	73	70	76	72	70	69						69													
10	83	76	71	68	82	75	71	68	75	71	68	74	70	68	73	70	68	67						67													

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2213601
5°	2202852
10°	2082173
15°	1770115
20°	1206459
25°	503381
30°	158285
35°	73561
40°	40678
45°	18650
50°	9060
55°	4953
60°	2579
65°	931
70°	383
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 18650 cd/sqm



TEST NUMBER: P769679

CATALOG NUMBER: LD6D65D010-EU6DR4055659030-6LBS1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1875.4	21.6
10°-20°	4201.4	48.3
20°-30°	2103.1	24.2
30°-40°	385.5	4.4
40°-50°	106.4	1.2
50°-60°	25.0	0.3
60°-70°	4.8	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	8179.9	94.0
0°-40°	8565.4	98.4
0°-60°	8696.7	99.9
0°-90°	8701.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8701.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	20260	
5°	20085	###
15°	15649	4201
25°	4176	2103
35°	552	386
45°	121	106
55°	26	25
65°	4	5
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P769679

CATALOG NUMBER: LD6D65D010-EU6DR4055659030-6LBS1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	20259.8
2.5°	20230.3
5°	20084.7
7.5°	19620.7
10°	18767.4
12.5°	17437.1
15°	15648.8
17.5°	13323.1
20°	10376.1
22.5°	7074.0
25°	4175.5
27.5°	2207.3
30°	1254.6
32.5°	810.7
35°	551.5
37.5°	394.1
40°	285.2
42.5°	195.3
45°	120.7
47.5°	76.9
50°	53.3
52.5°	37.9
55°	26.0
57.5°	16.6
60°	11.8
62.5°	7.1
65°	3.6
67.5°	2.4
70°	1.2
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)