

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P771665

Luminaire Tested: LD6D75BD010-EU6DR6570959050-6LBDP1LI

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P771665  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD6D75BD010-EU6DR6570959050-6LBDP1LI  
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 65° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 8362.0 lumens  
Efficiency: N/A  
Efficacy: 115.5 lumens/watt  
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 72.4  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



Downlight

TEST NUMBER: P771665  
CATALOG NUMBER: LD6D75BD010-EU6DR6570959050-6LBDP1LI

### Luminous Intensity Polar Plot





TEST NUMBER: P771665

CATALOG NUMBER: LD6D75BD010-EU6DR6570959050-6LBDP1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93																			
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87																			
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80																			
4	97	89	84	79	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	83	78	73	90	83	77	73	81	76	72	79	75	72	77	74	71	69																			
6	87	78	72	68	86	77	72	68	76	71	67	74	70	67	73	69	66	65																			
7	83	73	67	63	81	73	67	63	71	66	62	70	66	62	69	65	62	60																			
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	57																			
9	75	65	59	55	74	65	59	55	64	58	55	63	58	55	62	58	54	53																			
10	71	61	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	899544
5°	900293
10°	931993
15°	933527
20°	859466
25°	732317
30°	560607
35°	396067
40°	233784
45°	94905
50°	34404
55°	19163
60°	10992
65°	6050
70°	6357
75°	4939
80°	5160
85°	4388

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 94905 cd/sqm



TEST NUMBER: P771665

CATALOG NUMBER: LD6D75BD010-EU6DR6570959050-6LBDP1LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	792.8	9.5
10°-20°	2286.8	27.3
20°-30°	2743.7	32.8
30°-40°	1843.8	22.1
40°-50°	552.0	6.6
50°-60°	97.4	1.2
60°-70°	27.7	0.3
70°-80°	13.6	0.2
80°-90°	4.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5823.3	69.6
0°-40°	7667.1	91.7
0°-60°	8316.5	99.5
0°-90°	8362.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8362.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	8233	
5°	8208	793
15°	8253	2287
25°	6074	2744
35°	2969	1844
45°	614	552
55°	101	97
65°	23	28
75°	12	14
85°	4	4
90°	0	



TEST NUMBER: P771665

CATALOG NUMBER: LD6D75BD010-EU6DR6570959050-6LBDP1LI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	8233.0
2.5°	8268.1
5°	8208.5
7.5°	8332.5
10°	8400.4
12.5°	8384.0
15°	8252.9
17.5°	7932.4
20°	7391.8
22.5°	6755.4
25°	6074.5
27.5°	5305.8
30°	4443.5
32.5°	3662.0
35°	2969.4
37.5°	2284.9
40°	1639.1
42.5°	1070.5
45°	614.2
47.5°	325.3
50°	202.4
52.5°	140.4
55°	100.6
57.5°	72.5
60°	50.3
62.5°	32.8
65°	23.4
67.5°	21.1
70°	19.9
72.5°	15.2
75°	11.7
77.5°	10.5
80°	8.2
82.5°	5.8
85°	3.5
87.5°	2.3
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)