

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P770070

Luminaire Tested: LD6D65D010-EU6DR6555659030-6LBS1LI

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P770070  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD6D65D010-EU6DR6555659030-6LBS1LI  
Description: 6 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 65° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7669.1 lumens  
Efficiency: N/A  
Efficacy: 105.3 lumens/watt  
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96  
Luminous Opening: Circular (Dia: 0.48' x H: 0')  
CIE Type: Direct


Input Watts (W): 72.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



Downlight

TEST NUMBER: P770070  
CATALOG NUMBER: LD6D65D010-EU6DR6555659030-6LBS1LI

### Luminous Intensity Polar Plot





TEST NUMBER: P770070  
 CATALOG NUMBER: LD6D65D010-EU6DR6555659030-6LBS1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93																			
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85																			
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78																			
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72																			
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66																			
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61																			
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56																			
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52																			
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49																			
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	406690
5°	405663
10°	405313
15°	392823
20°	357617
25°	311639
30°	259195
35°	205374
40°	148227
45°	93647
50°	48810
55°	25945
60°	13631
65°	7490
70°	3142
75°	3453
80°	2422
85°	2077

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 93647 cd/sqm



TEST NUMBER: P770070

CATALOG NUMBER: LD6D65D010-EU6DR6555659030-6LBS1LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	658.5	8.6
10°-20°	1803.3	23.5
20°-30°	2204.2	28.7
30°-40°	1788.4	23.3
40°-50°	891.2	11.6
50°-60°	248.6	3.2
60°-70°	56.5	0.7
70°-80°	14.7	0.2
80°-90°	3.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4666.0	60.8
0°-40°	6454.4	84.2
0°-60°	7594.2	99.0
0°-90°	7669.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7669.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	6963	
5°	6919	659
15°	6497	1803
25°	4836	2204
35°	2880	1788
45°	1134	891
55°	255	249
65°	54	56
75°	15	15
85°	3	4
90°	0	



TEST NUMBER: P770070

CATALOG NUMBER: LD6D65D010-EU6DR6555659030-6LBS1LI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	6963.4
2.5°	6958.3
5°	6919.4
7.5°	6896.9
10°	6834.4
12.5°	6707.6
15°	6496.8
17.5°	6167.3
20°	5753.9
22.5°	5307.7
25°	4836.0
27.5°	4331.5
30°	3843.4
32.5°	3361.5
35°	2880.5
37.5°	2400.6
40°	1944.2
42.5°	1516.5
45°	1133.8
47.5°	790.0
50°	537.2
52.5°	370.4
55°	254.8
57.5°	171.9
60°	116.7
62.5°	80.8
65°	54.2
67.5°	27.6
70°	18.4
72.5°	17.4
75°	15.3
77.5°	10.2
80°	7.2
82.5°	5.1
85°	3.1
87.5°	2.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)