

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P770170

Luminaire Tested: LD6D65D010-EU6DR7055659040-6LBDP1LI

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P770170
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D65D010-EU6DR7055659040-6LBDP1LI
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8877.9 lumens
Efficiency: N/A
Efficacy: 121.9 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 72.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P770170
CATALOG NUMBER: LD6D65D010-EU6DR7055659040-6LBDP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P770170
 CATALOG NUMBER: LD6D65D010-EU6DR7055659040-6LBDP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91				
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83				
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76				
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70				
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65				
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61				
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57				
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53				
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50				
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48				

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1090553
5°	1058152
10°	1028661
15°	1015162
20°	947949
25°	712148
30°	503430
35°	178319
40°	93765
45°	99865
50°	103416
55°	105360
60°	106027
65°	103775
70°	97946
75°	90720
80°	80539
85°	65439

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 106048 cd/sqm



TEST NUMBER: P770170

CATALOG NUMBER: LD6D65D010-EU6DR7055659040-6LBDP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	910.0	10.3
10°-20°	2496.1	28.1
20°-30°	2749.1	31.0
30°-40°	1050.3	11.8
40°-50°	495.9	5.6
50°-60°	493.1	5.6
60°-70°	394.8	4.4
70°-80°	226.9	2.6
80°-90°	61.7	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6155.1	69.3
0°-40°	7205.5	81.2
0°-60°	8194.5	92.3
0°-90°	8877.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8877.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	9981	
5°	9648	910
15°	8975	2496
25°	5907	2749
35°	1337	1050
45°	646	496
55°	553	493
65°	401	395
75°	215	227
85°	52	62
90°	0	



TEST NUMBER: P770170

CATALOG NUMBER: LD6D65D010-EU6DR7055659040-6LBDP1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	9981.2
2.5°	9876.9
5°	9647.8
7.5°	9456.6
10°	9271.7
12.5°	9115.2
15°	8974.6
17.5°	8634.8
20°	8152.8
22.5°	7113.0
25°	5907.2
27.5°	5142.3
30°	3990.3
32.5°	2577.5
35°	1336.9
37.5°	722.2
40°	657.4
42.5°	652.7
45°	646.3
47.5°	632.1
50°	608.4
52.5°	581.6
55°	553.1
57.5°	521.5
60°	485.2
62.5°	444.1
65°	401.4
67.5°	354.0
70°	306.6
72.5°	259.2
75°	214.9
77.5°	169.1
80°	128.0
82.5°	90.1
85°	52.2
87.5°	20.5
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)