

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P770743

Luminaire Tested: LD6D70BD010-EU6DR6070959024-6LBDP1MW

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P770743
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D70BD010-EU6DR6070959024-6LBDP1MW
Description: 6 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6281.5 lumens
Efficiency: N/A
Efficacy: 94.3 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 66.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P770743
CATALOG NUMBER: LD6D70BD010-EU6DR6070959024-6LBDP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P770743

CATALOG NUMBER: LD6D70BD010-EU6DR6070959024-6LBDP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93																			
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86																			
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80																			
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70																			
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66																			
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62																			
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59																			
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55																			
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	815085
5°	835133
10°	845222
15°	805187
20°	709927
25°	574208
30°	388407
35°	194632
40°	31578
45°	30904
50°	31514
55°	32002
60°	32887
65°	33635
70°	34437
75°	34827
80°	33600
85°	27956

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 75°
 Luminance: 34827 cd/sqm



TEST NUMBER: P770743

CATALOG NUMBER: LD6D70BD010-EU6DR6070959024-6LBDP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	727.7	11.6
10°-20°	1969.0	31.3
20°-30°	2118.4	33.7
30°-40°	920.9	14.7
40°-50°	154.7	2.5
50°-60°	150.4	2.4
60°-70°	128.6	2.0
70°-80°	86.1	1.4
80°-90°	25.8	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4815.1	76.7
0°-40°	5736.0	91.3
0°-60°	6041.1	96.2
0°-90°	6281.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6281.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7460	
5°	7614	728
15°	7118	1969
25°	4763	2118
35°	1459	921
45°	200	155
55°	168	150
65°	130	129
75°	82	86
85°	22	26
90°	0	



TEST NUMBER: P770743

CATALOG NUMBER: LD6D70BD010-EU6DR6070959024-6LBDP1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	7460.0
2.5°	7669.7
5°	7614.4
7.5°	7631.9
10°	7618.3
12.5°	7461.0
15°	7118.3
17.5°	6658.1
20°	6105.7
22.5°	5514.4
25°	4763.0
27.5°	3809.6
30°	3078.6
32.5°	2372.8
35°	1459.2
37.5°	624.3
40°	221.4
42.5°	203.9
45°	200.0
47.5°	193.2
50°	185.4
52.5°	176.7
55°	168.0
57.5°	159.2
60°	150.5
62.5°	140.8
65°	130.1
67.5°	119.4
70°	107.8
72.5°	95.1
75°	82.5
77.5°	68.0
80°	53.4
82.5°	37.9
85°	22.3
87.5°	7.8
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)