

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P759787

Luminaire Tested: LD6D08D010-EU6DR700210IC9027-6LBDP1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P759787
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D08D010-EU6DR700210IC9027-6LBDP1B
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 442.2 lumens
Efficiency: N/A
Efficacy: 49.7 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 8.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P759787

CATALOG NUMBER: LD6D08D010-EU6DR700210IC9027-6LBDP1B

Luminous Intensity Polar Plot





TEST NUMBER: P759787

CATALOG NUMBER: LD6D08D010-EU6DR700210IC9027-6LBDP1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	54314
5°	52700
10°	51235
15°	50562
20°	47218
25°	35468
30°	25081
35°	8883
40°	4678
45°	4975
50°	5150
55°	5258
60°	5288
65°	5171
70°	4888
75°	4517
80°	4027
85°	3259

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 60°
 Luminance: 5288 cd/sqm



TEST NUMBER: P759787

CATALOG NUMBER: LD6D08D010-EU6DR700210IC9027-6LBDP1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	45.3	10.2
10°-20°	124.3	28.1
20°-30°	136.9	31.0
30°-40°	52.3	11.8
40°-50°	24.7	5.6
50°-60°	24.6	5.6
60°-70°	19.7	4.4
70°-80°	11.3	2.6
80°-90°	3.1	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	306.6	69.3
0°-40°	358.9	81.2
0°-60°	408.2	92.3
0°-90°	442.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	442.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	497	
5°	480	45
15°	447	124
25°	294	137
35°	67	52
45°	32	25
55°	28	25
65°	20	20
75°	11	11
85°	3	3
90°	0	



TEST NUMBER: P759787

CATALOG NUMBER: LD6D08D010-EU6DR700210IC9027-6LBDP1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	497.1
2.5°	491.9
5°	480.5
7.5°	471.0
10°	461.8
12.5°	454.0
15°	447.0
17.5°	430.1
20°	406.1
22.5°	354.3
25°	294.2
27.5°	256.1
30°	198.8
32.5°	128.4
35°	66.6
37.5°	36.0
40°	32.8
42.5°	32.5
45°	32.2
47.5°	31.5
50°	30.3
52.5°	29.0
55°	27.6
57.5°	26.0
60°	24.2
62.5°	22.1
65°	20.0
67.5°	17.6
70°	15.3
72.5°	12.9
75°	10.7
77.5°	8.4
80°	6.4
82.5°	4.5
85°	2.6
87.5°	1.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)