

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P758871

Luminaire Tested: LD6D08D010-EU6DR100210IC9030-6LBS1MW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P758871
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-4)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D08D010-EU6DR100210IC9030-6LBS1MW
Description: 6 INCH ROUND SHALLOW MATTE WHITE TRIM, WITH 10° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 769.6 lumens
Efficiency: N/A
Efficacy: 86.5 lumens/watt
Spacing Criteria (0/90/45): 0.17 / 0.17 / 0.18
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 8.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P758871
CATALOG NUMBER: LD6D08D010-EU6DR100210IC9030-6LBS1MW

Luminous Intensity Polar Plot





TEST NUMBER: P758871

CATALOG NUMBER: LD6D08D010-EU6DR100210IC9030-6LBS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20																	
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																					
RCR																																																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																																				
1	116	114	113	111	114	112	111	109	108	107	106	104	104	103	101	101	100	98																																				
2	113	110	108	106	111	108	106	104	105	104	102	103	101	100	99	98	98	97																																				
3	111	107	104	102	109	106	103	101	103	101	99	101	99	98	99	98	96	95																																				
4	108	104	101	99	107	103	100	98	101	99	97	99	97	96	98	96	94	93																																				
5	106	102	99	96	105	101	98	96	99	97	95	98	96	94	97	95	94	93																																				
6	104	100	96	94	103	99	96	94	98	95	93	97	94	93	96	94	92	91																																				
7	103	98	95	93	102	97	94	92	96	94	92	95	93	92	95	93	91	90																																				
8	101	96	93	91	100	96	93	91	95	92	91	94	92	90	93	92	90	89																																				
9	100	95	92	90	99	94	92	90	94	91	90	93	91	89	93	91	89	88																																				
10	98	94	91	89	98	93	91	89	93	90	88	92	90	88	92	90	88	87																																				

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1830861
5°	868190
10°	178058
15°	48888
20°	19697
25°	10561
30°	6245
35°	4068
40°	2710
45°	1762
50°	969
55°	724
60°	415
65°	0
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1762 cd/sqm



TEST NUMBER: P758871

CATALOG NUMBER: LD6D08D010-EU6DR100210IC9030-6LBS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	547.2	71.1
10°-20°	148.1	19.2
20°-30°	42.4	5.5
30°-40°	19.4	2.5
40°-50°	8.9	1.2
50°-60°	3.0	0.4
60°-70°	0.7	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	737.7	95.9
0°-40°	757.1	98.4
0°-60°	768.9	99.9
0°-90°	769.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	769.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	16757	
5°	7916	547
15°	432	148
25°	88	42
35°	30	19
45°	11	9
55°	4	3
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P758871

CATALOG NUMBER: LD6D08D010-EU6DR100210IC9030-6LBS1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	16756.8
0.5°	16612.1
1°	16240.9
1.5°	15525.1
2°	14723.6
2.5°	13665.1
3°	12488.6
3.5°	11350.2
4°	10122.2
4.5°	8991.4
5°	7915.8
5.5°	6941.1
6°	6012.0
6.5°	5195.3
7°	4426.2
7.5°	3769.4
8°	3186.9
8.5°	2676.7
9°	2235.0
9.5°	1898.0
10°	1604.9
12.5°	765.3
15°	432.2
17.5°	262.7
20°	169.4
22.5°	118.0
25°	87.6
27.5°	64.7
30°	49.5
32.5°	38.1
35°	30.5
37.5°	22.8
40°	19.0
42.5°	15.2
45°	11.4
47.5°	7.6
50°	5.7
52.5°	3.8
55°	3.8
57.5°	1.9
60°	1.9
62.5°	1.9
65°	0.0



TEST NUMBER: P758871
CATALOG NUMBER: LD6D08D010-EU6DR100210IC9030-6LBS1MW

CANDELA DISTRIBUTION (continued):

	0°
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



67.5°		0.0
70°		0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)