

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P758957

Luminaire Tested: LD6D08D010-EU6DR150210IC9035-6LBDP1LI

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P758957
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-21)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D08D010-EU6DR150210IC9035-6LBDP1LI
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 15° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 870.3 lumens
Efficiency: N/A
Efficacy: 97.8 lumens/watt
Spacing Criteria (0/90/45): 0.22 / 0.22 / 0.23
Luminous Opening: Vertical Cylinder (Dia: 0.35' x H: 0.35')
CIE Type: Direct

Input Watts (W): 8.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P758957

CATALOG NUMBER: LD6D08D010-EU6DR150210IC9035-6LBDP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P758957

CATALOG NUMBER: LD6D08D010-EU6DR150210IC9035-6LBDP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						100													
1	116	114	112	111	113	112	110	109	108	107	106	104	103	103	101	100	100	98						98													
2	113	110	107	105	111	108	106	104	105	103	102	102	101	100	100	98	98	96						96													
3	110	106	103	101	108	105	102	100	103	100	99	100	99	97	98	97	96	94						94													
4	108	103	100	98	106	102	99	97	100	98	96	99	97	95	97	95	94	93						93													
5	106	101	98	95	104	100	97	95	99	96	94	97	95	93	96	94	92	92						92													
6	104	99	95	93	102	98	95	93	97	94	92	96	93	92	95	93	91	90						90													
7	102	97	94	91	101	96	93	91	95	93	91	94	92	90	93	91	90	89						89													
8	100	95	92	90	99	95	92	90	94	91	89	93	91	89	92	90	89	88						88													
9	99	93	90	88	98	93	90	88	92	90	88	92	89	88	91	89	88	87						87													
10	97	92	89	87	96	92	89	87	91	89	87	91	88	87	90	88	86	86						86													

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1334273	1334273	1334273
5°	784077	773924	780053
10°	234015	235648	239259
15°	58211	59341	57508
20°	17412	20169	17788
25°	6139	7821	6216
30°	2254	2973	2291
35°	1133	1278	1097
40°	710	781	710
45°	525	560	525
50°	417	417	417
55°	348	348	348
60°	281	281	281
65°	214	214	214
70°	183	183	183
75°	113	113	151
80°	79	79	79
85°	42	42	42

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°

Vertical Angle: 45°

Luminance: 560 cd/sqm



TEST NUMBER: P758957

CATALOG NUMBER: LD6D08D010-EU6DR150210IC9035-6LBDP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	564.5	64.9
10°-20°	232.2	26.7
20°-30°	46.1	5.3
30°-40°	11.5	1.3
40°-50°	6.0	0.7
50°-60°	4.5	0.5
60°-70°	3.2	0.4
70°-80°	1.8	0.2
80°-90°	0.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	842.8	96.8
0°-40°	854.3	98.2
0°-60°	864.8	99.4
0°-90°	870.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	870.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	11858	11858	11858	11858	11858	
5°	7715	7636	7615	7668	7676	563
15°	670	683	683	671	662	230
25°	79	89	100	89	80	41
35°	16	17	18	17	15	11
45°	8	8	8	8	8	6
55°	5	5	5	5	5	4
65°	3	3	3	3	3	3
75°	2	2	2	2	2	2
85°	0	0	0	0	0	1
90°	0	0	0	0	0	



TEST NUMBER: P758957

CATALOG NUMBER: LD6D08D010-EU6DR150210IC9035-6LBDP1LI

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	11858.1	11858.1	11858.1	11858.1	11858.1
2.5°	10696.4	10705.5	10709.0	10719.5	10758.7
5°	7715.1	7635.8	7615.2	7667.9	7675.5
7.5°	4570.1	4586.2	4644.9	4658.0	4610.8
10°	2508.0	2528.5	2525.5	2543.6	2564.2
12.5°	1282.6	1266.5	1261.5	1282.1	1253.5
15°	670.2	682.7	683.2	671.2	662.1
17.5°	360.4	375.0	399.1	379.5	349.4
20°	212.8	225.9	246.5	230.4	217.4
22.5°	131.5	142.1	156.6	144.1	133.5
25°	78.8	89.4	100.4	88.9	79.8
27.5°	46.7	55.7	62.7	55.2	46.2
30°	30.1	35.1	39.7	34.6	30.6
32.5°	21.1	23.1	25.1	23.1	21.1
35°	15.6	16.6	17.6	16.6	15.1
37.5°	12.0	13.1	13.6	12.5	11.5
40°	10.0	10.5	11.0	10.5	10.0
42.5°	8.5	9.0	9.0	9.0	8.5
45°	7.5	7.5	8.0	7.5	7.5
47.5°	6.5	6.5	7.0	6.5	6.5
50°	6.0	6.0	6.0	6.0	6.0
52.5°	5.5	5.5	5.5	5.5	5.5
55°	5.0	5.0	5.0	5.0	5.0
57.5°	4.5	4.5	4.5	4.5	4.5
60°	4.0	4.0	4.0	4.0	4.0
62.5°	3.5	3.5	3.5	3.5	3.5
65°	3.0	3.0	3.0	3.0	3.0
67.5°	3.0	3.0	3.0	3.0	3.0
70°	2.5	2.5	2.5	2.5	2.5
72.5°	2.0	2.0	2.0	2.0	2.0
75°	1.5	1.5	1.5	1.5	2.0
77.5°	1.5	1.5	1.5	1.5	1.5
80°	1.0	1.0	1.0	1.0	1.0
82.5°	1.0	1.0	1.0	1.0	1.0
85°	0.5	0.5	0.5	0.5	0.5
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - - 90°-270°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)