

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P770925

Luminaire Tested: LD6D70BD010-EU6DR7070959030-6LBDP1MW

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P770925  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD6D70BD010-EU6DR7070959030-6LBDP1MW  
Description: 6 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 70° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6364.1 lumens  
Efficiency: N/A  
Efficacy: 95.6 lumens/watt  
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct


Input Watts (W): 66.6  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



Downlight

TEST NUMBER: P770925  
CATALOG NUMBER: LD6D70BD010-EU6DR7070959030-6LBDP1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P770925  
 CATALOG NUMBER: LD6D70BD010-EU6DR7070959030-6LBDP1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91				
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83				
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76				
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70				
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65				
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61				
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57				
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53				
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50				
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48				

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	781772
5°	758534
10°	737393
15°	727726
20°	679545
25°	510506
30°	360878
35°	127834
40°	67221
45°	71588
50°	74128
55°	75529
60°	76002
65°	74380
70°	70217
75°	65053
80°	57761
85°	46886

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 57.5°  
 Luminance: 76013 cd/sqm



TEST NUMBER: P770925

CATALOG NUMBER: LD6D70BD010-EU6DR7070959030-6LBDP1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	652.3	10.3
10°-20°	1789.3	28.1
20°-30°	1970.7	31.0
30°-40°	752.9	11.8
40°-50°	355.5	5.6
50°-60°	353.4	5.6
60°-70°	283.0	4.4
70°-80°	162.7	2.6
80°-90°	44.2	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4412.3	69.3
0°-40°	5165.3	81.2
0°-60°	5874.2	92.3
0°-90°	6364.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6364.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	7155	
5°	6916	652
15°	6434	1789
25°	4235	1971
35°	958	753
45°	463	356
55°	396	353
65°	288	283
75°	154	163
85°	37	44
90°	0	



TEST NUMBER: P770925

CATALOG NUMBER: LD6D70BD010-EU6DR7070959030-6LBDP1MW

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	7155.1
2.5°	7080.3
5°	6916.0
7.5°	6779.0
10°	6646.4
12.5°	6534.3
15°	6433.5
17.5°	6189.9
20°	5844.4
22.5°	5099.0
25°	4234.6
27.5°	3686.3
30°	2860.4
32.5°	1847.7
35°	958.4
37.5°	517.7
40°	471.3
42.5°	467.9
45°	463.3
47.5°	453.1
50°	436.1
52.5°	416.9
55°	396.5
57.5°	373.8
60°	347.8
62.5°	318.3
65°	287.7
67.5°	253.8
70°	219.8
72.5°	185.8
75°	154.1
77.5°	121.2
80°	91.8
82.5°	64.6
85°	37.4
87.5°	14.7
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)