

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P759677

Luminaire Tested: LD6D08D010-EU6DR600210IC9040-6LBS1MW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P759677
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-60)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D08D010-EU6DR600210IC9040-6LBS1MW
Description: 6 INCH ROUND SHALLOW MATTE WHITE TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 846.1 lumens
Efficiency: N/A
Efficacy: 95.1 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 8.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P759677
CATALOG NUMBER: LD6D08D010-EU6DR600210IC9040-6LBS1MW

Luminous Intensity Polar Plot





TEST NUMBER: P759677

CATALOG NUMBER: LD6D08D010-EU6DR600210IC9040-6LBS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR	0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100	100	100													
	1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94	94	94	94	94	94													
	2	108	103	99	96	106	101	98	95	98	95	92	95	93	90	92	90	89	87	87	87	87	87	87													
	3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81	81	81	81	81	81													
	4	97	90	84	80	95	88	83	79	86	82	78	84	81	78	82	79	77	75	75	75	75	75	75													
	5	92	84	78	74	91	83	77	73	81	76	73	79	75	72	78	74	71	70	70	70	70	70	70													
	6	88	79	73	68	86	78	72	68	76	71	68	75	70	67	74	70	67	65	65	65	65	65	65													
	7	83	74	68	63	82	73	67	63	72	67	63	71	66	63	69	65	62	61	61	61	61	61	61													
	8	79	69	63	59	78	69	63	59	68	63	59	67	62	59	66	61	58	57	57	57	57	57	57													
	9	75	65	59	55	74	65	59	55	64	59	55	63	58	55	62	58	55	53	53	53	53	53	53													
	10	72	62	56	52	71	61	56	52	61	55	52	60	55	52	59	55	52	50	50	50	50	50	50													

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	92522
5°	92283
10°	95358
15°	95446
20°	87833
25°	74696
30°	56912
35°	40255
40°	23634
45°	9534
50°	3179
55°	1524
60°	634
65°	78
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 9534 cd/sqm



TEST NUMBER: P759677

CATALOG NUMBER: LD6D08D010-EU6DR600210IC9040-6LBS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	81.2	9.6
10°-20°	233.8	27.6
20°-30°	279.8	33.1
30°-40°	187.1	22.1
40°-50°	55.5	6.6
50°-60°	8.0	0.9
60°-70°	0.7	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	594.7	70.3
0°-40°	781.9	92.4
0°-60°	845.3	99.9
0°-90°	846.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	846.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	847	
5°	841	81
15°	844	234
25°	620	280
35°	302	187
45°	62	55
55°	8	8
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P759677

CATALOG NUMBER: LD6D08D010-EU6DR600210IC9040-6LBS1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	846.8
2.5°	845.7
5°	841.4
7.5°	852.8
10°	859.5
12.5°	858.3
15°	843.8
17.5°	809.9
20°	755.4
22.5°	689.9
25°	619.6
27.5°	540.5
30°	451.1
32.5°	371.4
35°	301.8
37.5°	232.0
40°	165.7
42.5°	109.3
45°	61.7
47.5°	31.6
50°	18.7
52.5°	12.1
55°	8.0
57.5°	5.2
60°	2.9
62.5°	1.2
65°	0.3
67.5°	0.1
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)