

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P759829

Luminaire Tested: LD6D08D010-EU6DR700210IC9040-6LBDP1MW

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P759829  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD6D08D010-EU6DR700210IC9040-6LBDP1MW  
Description: 6 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 70° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 665.0 lumens  
Efficiency: N/A  
Efficacy: 74.7 lumens/watt  
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 8.9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight



TEST NUMBER: P759829

CATALOG NUMBER: LD6D08D010-EU6DR700210IC9040-6LBDP1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P759829

CATALOG NUMBER: LD6D08D010-EU6DR700210IC9040-6LBDP1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	81683
5°	79264
10°	77052
15°	76036
20°	71008
25°	53346
30°	37710
35°	13365
40°	7017
45°	7479
50°	7734
55°	7886
60°	7932
65°	7782
70°	7348
75°	6797
80°	6040
85°	4889

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 57.5°  
 Luminance: 7951 cd/sqm



TEST NUMBER: P759829

CATALOG NUMBER: LD6D08D010-EU6DR700210IC9040-6LBDP1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	68.2	10.2
10°-20°	187.0	28.1
20°-30°	205.9	31.0
30°-40°	78.7	11.8
40°-50°	37.1	5.6
50°-60°	36.9	5.6
60°-70°	29.6	4.4
70°-80°	17.0	2.6
80°-90°	4.6	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	461.1	69.3
0°-40°	539.7	81.2
0°-60°	613.8	92.3
0°-90°	665.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	665.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	748	
5°	723	68
15°	672	187
25°	442	206
35°	100	79
45°	48	37
55°	41	37
65°	30	30
75°	16	17
85°	4	5
90°	0	



TEST NUMBER: P759829

CATALOG NUMBER: LD6D08D010-EU6DR700210IC9040-6LBDP1MW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	747.6
2.5°	739.8
5°	722.7
7.5°	708.3
10°	694.5
12.5°	682.8
15°	672.2
17.5°	646.8
20°	610.7
22.5°	532.8
25°	442.5
27.5°	385.2
30°	298.9
32.5°	193.1
35°	100.2
37.5°	54.1
40°	49.2
42.5°	48.9
45°	48.4
47.5°	47.3
50°	45.5
52.5°	43.5
55°	41.4
57.5°	39.1
60°	36.3
62.5°	33.3
65°	30.1
67.5°	26.5
70°	23.0
72.5°	19.4
75°	16.1
77.5°	12.7
80°	9.6
82.5°	6.8
85°	3.9
87.5°	1.5
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)