

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P770874

Luminaire Tested: LD6D70BD010-EU6DR6570959040-6LBS1B

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P770874
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D70BD010-EU6DR6570959040-6LBS1B
Description: 6 INCH ROUND SHALLOW SPECULAR BLACK TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7311.9 lumens
Efficiency: N/A
Efficacy: 109.8 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct


Input Watts (W): 66.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P770874
CATALOG NUMBER: LD6D70BD010-EU6DR6570959040-6LBS1B

Luminous Intensity Polar Plot





TEST NUMBER: P770874
 CATALOG NUMBER: LD6D70BD010-EU6DR6570959040-6LBS1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93			93																
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85			85																
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78			78																
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72			72																
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66			66																
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61			61																
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56			56																
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52			52																
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49			49																
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46			46																

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	387743
5°	386762
10°	386430
15°	374521
20°	340954
25°	297121
30°	247123
35°	195806
40°	141320
45°	89286
50°	46539
55°	24733
60°	12989
65°	7145
70°	3005
75°	3295
80°	2287
85°	1943

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 89286 cd/sqm



TEST NUMBER: P770874

CATALOG NUMBER: LD6D70BD010-EU6DR6570959040-6LBS1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	627.8	8.6
10°-20°	1719.3	23.5
20°-30°	2101.5	28.7
30°-40°	1705.1	23.3
40°-50°	849.7	11.6
50°-60°	237.0	3.2
60°-70°	53.9	0.7
70°-80°	14.0	0.2
80°-90°	3.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4448.6	60.8
0°-40°	6153.7	84.2
0°-60°	7240.4	99.0
0°-90°	7311.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7311.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6639	
5°	6597	628
15°	6194	1719
25°	4611	2102
35°	2746	1705
45°	1081	850
55°	243	237
65°	52	54
75°	15	14
85°	3	4
90°	0	



TEST NUMBER: P770874

CATALOG NUMBER: LD6D70BD010-EU6DR6570959040-6LBS1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	6639.0
2.5°	6634.1
5°	6597.0
7.5°	6575.6
10°	6516.0
12.5°	6395.1
15°	6194.1
17.5°	5879.9
20°	5485.8
22.5°	5060.4
25°	4610.7
27.5°	4129.7
30°	3664.4
32.5°	3204.8
35°	2746.3
37.5°	2288.8
40°	1853.6
42.5°	1445.8
45°	1081.0
47.5°	753.2
50°	512.2
52.5°	353.2
55°	242.9
57.5°	163.9
60°	111.2
62.5°	77.1
65°	51.7
67.5°	26.3
70°	17.6
72.5°	16.6
75°	14.6
77.5°	9.8
80°	6.8
82.5°	4.9
85°	2.9
87.5°	2.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)