

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P770950

Luminaire Tested: LD6D70BD010-EU6DR7070959040-6LBDP1LI

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P770950  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD6D70BD010-EU6DR7070959040-6LBDP1LI  
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 70° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 9049.4 lumens  
Efficiency: N/A  
Efficacy: 135.9 lumens/watt  
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct


Input Watts (W): 66.6  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



Downlight

TEST NUMBER: P770950  
CATALOG NUMBER: LD6D70BD010-EU6DR7070959040-6LBDP1LI

### Luminous Intensity Polar Plot





TEST NUMBER: P770950

CATALOG NUMBER: LD6D70BD010-EU6DR7070959040-6LBDP1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91		
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83		
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76		
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70		
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65		
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61		
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57		
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53		
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50		
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48		

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1111630
5°	1078596
10°	1048531
15°	1034777
20°	966262
25°	725903
30°	513157
35°	181774
40°	95576
45°	101796
50°	105421
55°	107398
60°	108059
65°	105792
70°	99830
75°	92493
80°	82112
85°	66693

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 57.5°  
 Luminance: 108102 cd/sqm



TEST NUMBER: P770950

CATALOG NUMBER: LD6D70BD010-EU6DR7070959040-6LBDP1LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	927.6	10.3
10°-20°	2544.3	28.1
20°-30°	2802.2	31.0
30°-40°	1070.7	11.8
40°-50°	505.5	5.6
50°-60°	502.6	5.6
60°-70°	402.4	4.4
70°-80°	231.3	2.6
80°-90°	62.9	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6274.1	69.3
0°-40°	7344.7	81.2
0°-60°	8352.8	92.3
0°-90°	9049.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	9049.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	10174	
5°	9834	928
15°	9148	2544
25°	6021	2802
35°	1363	1071
45°	659	506
55°	564	503
65°	409	402
75°	219	231
85°	53	63
90°	0	



TEST NUMBER: P770950

CATALOG NUMBER: LD6D70BD010-EU6DR7070959040-6LBDP1LI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	10174.1
2.5°	10067.8
5°	9834.2
7.5°	9639.3
10°	9450.8
12.5°	9291.3
15°	9148.0
17.5°	8801.6
20°	8310.3
22.5°	7250.4
25°	6021.3
27.5°	5241.7
30°	4067.4
32.5°	2627.3
35°	1362.8
37.5°	736.2
40°	670.1
42.5°	665.3
45°	658.8
47.5°	644.3
50°	620.2
52.5°	592.8
55°	563.8
57.5°	531.6
60°	494.5
62.5°	452.6
65°	409.2
67.5°	360.8
70°	312.5
72.5°	264.2
75°	219.1
77.5°	172.4
80°	130.5
82.5°	91.8
85°	53.2
87.5°	20.9
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)