

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P771521

Luminaire Tested: LD6D75BD010-EU6DR6070959024-6LBDP1H

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P771521
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D75BD010-EU6DR6070959024-6LBDP1H
Description: 6 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7331.0 lumens
Efficiency: N/A
Efficacy: 101.3 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 72.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P771521
CATALOG NUMBER: LD6D75BD010-EU6DR6070959024-6LBDP1H

Luminous Intensity Polar Plot





TEST NUMBER: P771521

CATALOG NUMBER: LD6D75BD010-EU6DR6070959024-6LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93																			
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86																			
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80																			
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70																			
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66																			
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62																			
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59																			
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55																			
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	951290
5°	974676
10°	986446
15°	939726
20°	828549
25°	670158
30°	453305
35°	227151
40°	36841
45°	36065
50°	36784
55°	37336
60°	38372
65°	39245
70°	40188
75°	40653
80°	39200
85°	32720

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 75°
 Luminance: 40653 cd/sqm



TEST NUMBER: P771521

CATALOG NUMBER: LD6D75BD010-EU6DR6070959024-6LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	849.3	11.6
10°-20°	2298.0	31.3
20°-30°	2472.4	33.7
30°-40°	1074.7	14.7
40°-50°	180.5	2.5
50°-60°	175.5	2.4
60°-70°	150.1	2.0
70°-80°	100.4	1.4
80°-90°	30.1	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5619.7	76.7
0°-40°	6694.4	91.3
0°-60°	7050.4	96.2
0°-90°	7331.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7331.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8707	
5°	8887	849
15°	8308	2298
25°	5559	2472
35°	1703	1075
45°	233	180
55°	196	175
65°	152	150
75°	96	100
85°	26	30
90°	0	



TEST NUMBER: P771521

CATALOG NUMBER: LD6D75BD010-EU6DR6070959024-6LBDP1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	8706.6
2.5°	8951.3
5°	8886.7
7.5°	8907.1
10°	8891.2
12.5°	8707.7
15°	8307.7
17.5°	7770.6
20°	7125.9
22.5°	6435.9
25°	5558.9
27.5°	4446.2
30°	3593.0
32.5°	2769.2
35°	1703.0
37.5°	728.6
40°	258.3
42.5°	237.9
45°	233.4
47.5°	225.5
50°	216.4
52.5°	206.2
55°	196.0
57.5°	185.8
60°	175.6
62.5°	164.3
65°	151.8
67.5°	139.4
70°	125.8
72.5°	111.0
75°	96.3
77.5°	79.3
80°	62.3
82.5°	44.2
85°	26.1
87.5°	9.1
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)