

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P771612

Luminaire Tested: LD6D75BD010-EU6DR6570959027-6LBDP1H

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P771612
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D75BD010-EU6DR6570959027-6LBDP1H
Description: 6 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7256.2 lumens
Efficiency: N/A
Efficacy: 100.2 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 72.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P771612
CATALOG NUMBER: LD6D75BD010-EU6DR6570959027-6LBDP1H

Luminous Intensity Polar Plot





TEST NUMBER: P771612
 CATALOG NUMBER: LD6D75BD010-EU6DR6570959027-6LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93																			
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87																			
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80																			
4	97	89	84	79	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	83	78	73	90	83	77	73	81	76	72	79	75	72	77	74	71	69																			
6	87	78	72	68	86	77	72	68	76	71	67	74	70	67	73	69	66	65																			
7	83	73	67	63	81	73	67	63	71	66	62	70	66	62	69	65	62	60																			
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	57																			
9	75	65	59	55	74	65	59	55	64	58	55	63	58	55	62	58	54	53																			
10	71	61	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	780581
5°	781226
10°	808732
15°	810073
20°	745809
25°	635462
30°	486474
35°	343687
40°	202877
45°	82358
50°	29848
55°	16630
60°	9549
65°	5248
70°	5527
75°	4306
80°	4467
85°	3761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 82358 cd/sqm



TEST NUMBER: P771612

CATALOG NUMBER: LD6D75BD010-EU6DR6570959027-6LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	687.9	9.5
10°-20°	1984.4	27.3
20°-30°	2380.9	32.8
30°-40°	1600.0	22.1
40°-50°	479.0	6.6
50°-60°	84.5	1.2
60°-70°	24.0	0.3
70°-80°	11.8	0.2
80°-90°	3.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5053.2	69.6
0°-40°	6653.2	91.7
0°-60°	7216.6	99.5
0°-90°	7256.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7256.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7144	
5°	7123	688
15°	7162	1984
25°	5271	2381
35°	2577	1600
45°	533	479
55°	87	85
65°	20	24
75°	10	12
85°	3	4
90°	0	



TEST NUMBER: P771612
CATALOG NUMBER: LD6D75BD010-EU6DR6570959027-6LBDP1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	7144.2
2.5°	7174.7
5°	7122.9
7.5°	7230.5
10°	7289.4
12.5°	7275.2
15°	7161.5
17.5°	6883.3
20°	6414.3
22.5°	5862.0
25°	5271.1
27.5°	4604.1
30°	3855.9
32.5°	3177.7
35°	2576.7
37.5°	1982.8
40°	1422.4
42.5°	928.9
45°	533.0
47.5°	282.2
50°	175.6
52.5°	121.8
55°	87.3
57.5°	62.9
60°	43.7
62.5°	28.4
65°	20.3
67.5°	18.3
70°	17.3
72.5°	13.2
75°	10.2
77.5°	9.1
80°	7.1
82.5°	5.1
85°	3.0
87.5°	2.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)