

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P771689

Luminaire Tested: LD6D75BD010-EU6DR7070959027-6LBDP1B

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P771689  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD6D75BD010-EU6DR7070959027-6LBDP1B  
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 70° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4863.4 lumens  
Efficiency: N/A  
Efficacy: 67.2 lumens/watt  
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct


Input Watts (W): 72.4  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



Downlight

TEST NUMBER: P771689  
CATALOG NUMBER: LD6D75BD010-EU6DR7070959027-6LBDP1B

### Luminous Intensity Polar Plot





TEST NUMBER: P771689

CATALOG NUMBER: LD6D75BD010-EU6DR7070959027-6LBDP1B

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	597427
5°	579671
10°	563518
15°	556119
20°	519298
25°	390131
30°	275781
35°	97690
40°	51361
45°	54715
50°	56654
55°	57719
60°	58083
65°	56851
70°	53637
75°	49687
80°	44107
85°	35854

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 57.5°  
 Luminance: 58098 cd/sqm



TEST NUMBER: P771689

CATALOG NUMBER: LD6D75BD010-EU6DR7070959027-6LBDP1B

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	498.5	10.3
10°-20°	1367.4	28.1
20°-30°	1506.0	31.0
30°-40°	575.4	11.8
40°-50°	271.7	5.6
50°-60°	270.1	5.6
60°-70°	216.3	4.4
70°-80°	124.3	2.6
80°-90°	33.8	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3371.9	69.3
0°-40°	3947.3	81.2
0°-60°	4489.1	92.3
0°-90°	4863.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4863.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	5468	
5°	5285	499
15°	4916	1367
25°	3236	1506
35°	732	575
45°	354	272
55°	303	270
65°	220	216
75°	118	124
85°	29	34
90°	0	



TEST NUMBER: P771689

CATALOG NUMBER: LD6D75BD010-EU6DR7070959027-6LBDP1B

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	5467.9
2.5°	5410.7
5°	5285.2
7.5°	5180.5
10°	5079.2
12.5°	4993.5
15°	4916.4
17.5°	4730.3
20°	4466.2
22.5°	3896.6
25°	3236.1
27.5°	2817.0
30°	2185.9
32.5°	1412.0
35°	732.4
37.5°	395.6
40°	360.1
42.5°	357.5
45°	354.1
47.5°	346.3
50°	333.3
52.5°	318.6
55°	303.0
57.5°	285.7
60°	265.8
62.5°	243.3
65°	219.9
67.5°	193.9
70°	167.9
72.5°	142.0
75°	117.7
77.5°	92.6
80°	70.1
82.5°	49.3
85°	28.6
87.5°	11.3
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)