

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P772432

Luminaire Tested: LD6D80BD010-EU6DR6570959040-6LBDP1LI

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P772432  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD6D80BD010-EU6DR6570959040-6LBDP1LI  
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 65° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 9406.5 lumens  
Efficiency: N/A  
Efficacy: 119.2 lumens/watt  
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 78.9  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight

TEST NUMBER: P772432

CATALOG NUMBER: LD6D80BD010-EU6DR6570959040-6LBDP1LI

### Luminous Intensity Polar Plot





TEST NUMBER: P772432

CATALOG NUMBER: LD6D80BD010-EU6DR6570959040-6LBDP1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93																			
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87																			
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80																			
4	97	89	84	79	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	83	78	73	90	83	77	73	81	76	72	79	75	72	77	74	71	69																			
6	87	78	72	68	86	77	72	68	76	71	67	74	70	67	73	69	66	65																			
7	83	73	67	63	81	73	67	63	71	66	62	70	66	62	69	65	62	60																			
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	57																			
9	75	65	59	55	74	65	59	55	64	58	55	63	58	55	62	58	54	53																			
10	71	61	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1011897
5°	1012735
10°	1048387
15°	1050126
20°	966821
25°	823783
30°	630628
35°	445525
40°	262981
45°	106757
50°	38704
55°	21564
60°	12368
65°	6799
70°	7156
75°	5572
80°	5789
85°	4889

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 106757 cd/sqm



TEST NUMBER: P772432

CATALOG NUMBER: LD6D80BD010-EU6DR6570959040-6LBDP1LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	891.8	9.5
10°-20°	2572.4	27.3
20°-30°	3086.4	32.8
30°-40°	2074.1	22.1
40°-50°	620.9	6.6
50°-60°	109.6	1.2
60°-70°	31.2	0.3
70°-80°	15.3	0.2
80°-90°	4.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6550.6	69.6
0°-40°	8624.7	91.7
0°-60°	9355.2	99.5
0°-90°	9406.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	9406.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	9261	
5°	9234	892
15°	9284	2572
25°	6833	3086
35°	3340	2074
45°	691	621
55°	113	110
65°	26	31
75°	13	15
85°	4	5
90°	0	



TEST NUMBER: P772432

CATALOG NUMBER: LD6D80BD010-EU6DR6570959040-6LBDP1LI

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	9261.3
2.5°	9300.8
5°	9233.7
7.5°	9373.2
10°	9449.5
12.5°	9431.1
15°	9283.7
17.5°	8923.1
20°	8315.1
22.5°	7599.1
25°	6833.2
27.5°	5968.5
30°	4998.5
32.5°	4119.4
35°	3340.2
37.5°	2570.3
40°	1843.8
42.5°	1204.2
45°	690.9
47.5°	365.9
50°	227.7
52.5°	157.9
55°	113.2
57.5°	81.6
60°	56.6
62.5°	36.9
65°	26.3
67.5°	23.7
70°	22.4
72.5°	17.1
75°	13.2
77.5°	11.8
80°	9.2
82.5°	6.6
85°	3.9
87.5°	2.6
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)