

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P772434

Luminaire Tested: LD6D80BD010-EU6DR6570959040-6LBS1B

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P772434
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D80BD010-EU6DR6570959040-6LBS1B
Description: 6 INCH ROUND SHALLOW SPECULAR BLACK TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8755.4 lumens
Efficiency: N/A
Efficacy: 111.0 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct


Input Watts (W): 78.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P772434
CATALOG NUMBER: LD6D80BD010-EU6DR6570959040-6LBS1B

Luminous Intensity Polar Plot





TEST NUMBER: P772434

CATALOG NUMBER: LD6D80BD010-EU6DR6570959040-6LBS1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93			93
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85			85
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78			78
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72			72
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66			66
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61			61
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56			56
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52			52
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49			49
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46			46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	464293
5°	463124
10°	462726
15°	448462
20°	408271
25°	355782
30°	295909
35°	234463
40°	169224
45°	106912
50°	55725
55°	29621
60°	15559
65°	8554
70°	3586
75°	3949
80°	2758
85°	2345

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 106912 cd/sqm



TEST NUMBER: P772434

CATALOG NUMBER: LD6D80BD010-EU6DR6570959040-6LBS1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	751.8	8.6
10°-20°	2058.7	23.5
20°-30°	2516.4	28.7
30°-40°	2041.7	23.3
40°-50°	1017.5	11.6
50°-60°	283.8	3.2
60°-70°	64.5	0.7
70°-80°	16.8	0.2
80°-90°	4.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5326.9	60.8
0°-40°	7368.6	84.2
0°-60°	8669.9	99.0
0°-90°	8755.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8755.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7950	
5°	7900	752
15°	7417	2059
25°	5521	2516
35°	3288	2042
45°	1294	1017
55°	291	284
65°	62	64
75°	18	17
85°	4	4
90°	0	



TEST NUMBER: P772434

CATALOG NUMBER: LD6D80BD010-EU6DR6570959040-6LBS1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	7949.7
2.5°	7943.9
5°	7899.5
7.5°	7873.8
10°	7802.5
12.5°	7657.7
15°	7417.0
17.5°	7040.8
20°	6568.9
22.5°	6059.5
25°	5521.0
27.5°	4945.1
30°	4387.8
32.5°	3837.6
35°	3288.5
37.5°	2740.6
40°	2219.6
42.5°	1731.3
45°	1294.4
47.5°	901.9
50°	613.3
52.5°	422.9
55°	290.9
57.5°	196.3
60°	133.2
62.5°	92.3
65°	61.9
67.5°	31.5
70°	21.0
72.5°	19.9
75°	17.5
77.5°	11.7
80°	8.2
82.5°	5.8
85°	3.5
87.5°	2.3
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)