

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P772436

Luminaire Tested: LD6D80BD010-EU6DR6570959040-6LBS1LI

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P772436  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD6D80BD010-EU6DR6570959040-6LBS1LI  
Description: 6 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 65° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 9901.6 lumens  
Efficiency: N/A  
Efficacy: 125.5 lumens/watt  
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96  
Luminous Opening: Circular (Dia: 0.48' x H: 0')  
CIE Type: Direct


Input Watts (W): 78.9  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



Downlight

TEST NUMBER: P772436  
CATALOG NUMBER: LD6D80BD010-EU6DR6570959040-6LBS1LI

### Luminous Intensity Polar Plot





TEST NUMBER: P772436

CATALOG NUMBER: LD6D80BD010-EU6DR6570959040-6LBS1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93	93	93	93
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85	85	85	85
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78	78	78	78
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72	72	72	72
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66	66	66	66
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61	61	61	61
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56	56	56	56
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52	52	52	52
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49	49	49	49
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46	46	46	46

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	525068
5°	523744
10°	523300
15°	507167
20°	461716
25°	402354
30°	334646
35°	265157
40°	191380
45°	120903
50°	63021
55°	33500
60°	17591
65°	9674
70°	4064
75°	4468
80°	3094
85°	2680

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 120903 cd/sqm



TEST NUMBER: P772436

CATALOG NUMBER: LD6D80BD010-EU6DR6570959040-6LBS1LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	850.2	8.6
10°-20°	2328.2	23.5
20°-30°	2845.8	28.7
30°-40°	2309.0	23.3
40°-50°	1150.6	11.6
50°-60°	321.0	3.2
60°-70°	72.9	0.7
70°-80°	19.0	0.2
80°-90°	4.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6024.2	60.8
0°-40°	8333.2	84.2
0°-60°	9804.8	99.0
0°-90°	9901.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	9901.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	8990	
5°	8934	850
15°	8388	2328
25°	6244	2846
35°	3719	2309
45°	1464	1151
55°	329	321
65°	70	73
75°	20	19
85°	4	5
90°	0	



TEST NUMBER: P772436

CATALOG NUMBER: LD6D80BD010-EU6DR6570959040-6LBS1LI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	8990.3
2.5°	8983.7
5°	8933.5
7.5°	8904.5
10°	8823.9
12.5°	8660.1
15°	8387.9
17.5°	7962.5
20°	7428.8
22.5°	6852.7
25°	6243.7
27.5°	5592.4
30°	4962.2
32.5°	4339.9
35°	3719.0
37.5°	3099.4
40°	2510.2
42.5°	1957.9
45°	1463.8
47.5°	1019.9
50°	693.6
52.5°	478.3
55°	329.0
57.5°	222.0
60°	150.6
62.5°	104.4
65°	70.0
67.5°	35.7
70°	23.8
72.5°	22.5
75°	19.8
77.5°	13.2
80°	9.2
82.5°	6.6
85°	4.0
87.5°	2.6
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)