

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P771548

Luminaire Tested: LD6D75BD010-EU6DR6070959030-6LBDP1LI

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P771548
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D75BD010-EU6DR6070959030-6LBDP1LI
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8983.2 lumens
Efficiency: N/A
Efficacy: 124.1 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 72.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P771548

CATALOG NUMBER: LD6D75BD010-EU6DR6070959030-6LBDP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P771548

CATALOG NUMBER: LD6D75BD010-EU6DR6070959030-6LBDP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93																			
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86																			
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80																			
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70																			
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66																			
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62																			
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59																			
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55																			
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1165670
5°	1194329
10°	1208760
15°	1151511
20°	1015271
25°	821179
30°	555460
35°	278343
40°	45157
45°	44192
50°	45079
55°	45756
60°	47026
65°	48087
70°	49228
75°	49814
80°	48071
85°	39991

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 75°
 Luminance: 49814 cd/sqm



TEST NUMBER: P771548

CATALOG NUMBER: LD6D75BD010-EU6DR6070959030-6LBDP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1040.8	11.6
10°-20°	2815.8	31.3
20°-30°	3029.6	33.7
30°-40°	1316.9	14.7
40°-50°	221.2	2.5
50°-60°	215.1	2.4
60°-70°	183.9	2.0
70°-80°	123.1	1.4
80°-90°	36.8	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6886.2	76.7
0°-40°	8203.1	91.3
0°-60°	8639.4	96.2
0°-90°	8983.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8983.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	10669	
5°	10889	###
15°	10180	2816
25°	6812	3030
35°	2087	1317
45°	286	221
55°	240	215
65°	186	184
75°	118	123
85°	32	37
90°	0	



TEST NUMBER: P771548

CATALOG NUMBER: LD6D75BD010-EU6DR6070959030-6LBDP1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	10668.7
2.5°	10968.6
5°	10889.4
7.5°	10914.4
10°	10895.0
12.5°	10670.1
15°	10180.0
17.5°	9521.8
20°	8731.8
22.5°	7886.3
25°	6811.6
27.5°	5448.2
30°	4402.7
32.5°	3393.3
35°	2086.8
37.5°	892.8
40°	316.6
42.5°	291.6
45°	286.0
47.5°	276.3
50°	265.2
52.5°	252.7
55°	240.2
57.5°	227.7
60°	215.2
62.5°	201.3
65°	186.0
67.5°	170.8
70°	154.1
72.5°	136.1
75°	118.0
77.5°	97.2
80°	76.4
82.5°	54.1
85°	31.9
87.5°	11.1
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)