

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P772437

Luminaire Tested: LD6D80BD010-EU6DR6570959040-6LBS1MW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P772437
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D80BD010-EU6DR6570959040-6LBS1MW
Description: 6 INCH ROUND SHALLOW MATTE WHITE TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8960.7 lumens
Efficiency: N/A
Efficacy: 113.6 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct

Input Watts (W): 78.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P772437

CATALOG NUMBER: LD6D80BD010-EU6DR6570959040-6LBS1MW

Luminous Intensity Polar Plot





TEST NUMBER: P772437

CATALOG NUMBER: LD6D80BD010-EU6DR6570959040-6LBS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93			93																
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85			85																
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78			78																
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72			72																
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66			66																
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61			61																
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56			56																
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52			52																
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49			49																
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46			46																

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	475174
5°	473976
10°	473573
15°	458977
20°	417836
25°	364120
30°	302848
35°	239960
40°	173189
45°	109414
50°	57033
55°	30313
60°	15921
65°	8762
70°	3671
75°	4039
80°	2825
85°	2412

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 109414 cd/sqm



TEST NUMBER: P772437

CATALOG NUMBER: LD6D80BD010-EU6DR6570959040-6LBS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	769.4	8.6
10°-20°	2106.9	23.5
20°-30°	2575.4	28.7
30°-40°	2089.6	23.3
40°-50°	1041.3	11.6
50°-60°	290.4	3.2
60°-70°	66.0	0.7
70°-80°	17.2	0.2
80°-90°	4.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5451.8	60.8
0°-40°	7541.4	84.2
0°-60°	8873.1	99.0
0°-90°	8960.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8960.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8136	
5°	8085	769
15°	7591	2107
25°	5650	2575
35°	3366	2090
45°	1325	1041
55°	298	290
65°	63	66
75°	18	17
85°	4	4
90°	0	



TEST NUMBER: P772437

CATALOG NUMBER: LD6D80BD010-EU6DR6570959040-6LBS1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	8136.0
2.5°	8130.1
5°	8084.6
7.5°	8058.3
10°	7985.4
12.5°	7837.1
15°	7590.9
17.5°	7205.9
20°	6722.8
22.5°	6201.6
25°	5650.4
27.5°	5061.0
30°	4490.7
32.5°	3927.5
35°	3365.6
37.5°	2804.9
40°	2271.6
42.5°	1771.9
45°	1324.7
47.5°	923.0
50°	627.7
52.5°	432.8
55°	297.7
57.5°	200.9
60°	136.3
62.5°	94.5
65°	63.4
67.5°	32.3
70°	21.5
72.5°	20.3
75°	17.9
77.5°	12.0
80°	8.4
82.5°	6.0
85°	3.6
87.5°	2.4
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)