

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P771624

Luminaire Tested: LD6D75BD010-EU6DR6570959030-6LBDP1B

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P771624  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD6D75BD010-EU6DR6570959030-6LBDP1B  
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 65° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5568.4 lumens  
Efficiency: N/A  
Efficacy: 76.9 lumens/watt  
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 72.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight

TEST NUMBER: P771624

CATALOG NUMBER: LD6D75BD010-EU6DR6570959030-6LBDP1B

### Luminous Intensity Polar Plot





TEST NUMBER: P771624

CATALOG NUMBER: LD6D75BD010-EU6DR6570959030-6LBDP1B

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93																			
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87																			
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80																			
4	97	89	84	79	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	83	78	73	90	83	77	73	81	76	72	79	75	72	77	74	71	69																			
6	87	78	72	68	86	77	72	68	76	71	67	74	70	67	73	69	66	65																			
7	83	73	67	63	81	73	67	63	71	66	62	70	66	62	69	65	62	60																			
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	57																			
9	75	65	59	55	74	65	59	55	64	58	55	63	58	55	62	58	54	53																			
10	71	61	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50																			

**AVERAGE LUMINANCE (cd/sqm):**

0°	
0°	599022
5°	599512
10°	620622
15°	621646
20°	572330
25°	487661
30°	373318
35°	263738
40°	155680
45°	63198
50°	22913
55°	12763
60°	7320
65°	4033
70°	4217
75°	3293
80°	3461
85°	2883

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 63198 cd/sqm



TEST NUMBER: P771624

CATALOG NUMBER: LD6D75BD010-EU6DR6570959030-6LBDP1B

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	527.9	9.5
10°-20°	1522.8	27.3
20°-30°	1827.1	32.8
30°-40°	1227.8	22.1
40°-50°	367.6	6.6
50°-60°	64.9	1.2
60°-70°	18.4	0.3
70°-80°	9.0	0.2
80°-90°	2.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3877.8	69.6
0°-40°	5105.6	91.7
0°-60°	5538.1	99.5
0°-90°	5568.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5568.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	5482	
5°	5466	528
15°	5496	1523
25°	4045	1827
35°	1977	1228
45°	409	368
55°	67	65
65°	16	18
75°	8	9
85°	2	3
90°	0	



TEST NUMBER: P771624

CATALOG NUMBER: LD6D75BD010-EU6DR6570959030-6LBDP1B

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	5482.5
2.5°	5505.9
5°	5466.1
7.5°	5548.7
10°	5593.9
12.5°	5583.0
15°	5495.7
17.5°	5282.3
20°	4922.3
22.5°	4498.5
25°	4045.1
27.5°	3533.2
30°	2959.0
32.5°	2438.6
35°	1977.3
37.5°	1521.6
40°	1091.5
42.5°	712.9
45°	409.0
47.5°	216.6
50°	134.8
52.5°	93.5
55°	67.0
57.5°	48.3
60°	33.5
62.5°	21.8
65°	15.6
67.5°	14.0
70°	13.2
72.5°	10.1
75°	7.8
77.5°	7.0
80°	5.5
82.5°	3.9
85°	2.3
87.5°	1.6
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)