

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P771094

Luminaire Tested: LD6D75BD010-EU6DR3070959035-6LBDP1MW

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P771094  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-16)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD6D75BD010-EU6DR3070959035-6LBDP1MW  
Description: 6 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 30° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7510.0 lumens  
Efficiency: N/A  
Efficacy: 103.7 lumens/watt  
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.49  
Luminous Opening: Rectangular (W 0.38' x L: 0.38' x H: 0')  
CIE Type: Direct


Input Watts (W): 72.4  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



Downlight

TEST NUMBER: P771094  
CATALOG NUMBER: LD6D75BD010-EU6DR3070959035-6LBDP1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P771094

CATALOG NUMBER: LD6D75BD010-EU6DR3070959035-6LBDP1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						100													
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96						96													
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92						92													
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	89						89													
4	103	98	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87	85						85													
5	100	94	89	86	98	93	89	86	91	88	85	90	86	84	88	86	83	82						82													
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79						79													
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77						77													
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74						74													
9	88	81	76	73	87	80	76	73	80	76	73	79	75	73	78	75	73	72						72													
10	85	78	74	71	85	78	74	71	77	73	71	76	73	71	76	73	70	69						69													

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	1848401	1848401	1848401
5°	1795337	1793240	1795429
10°	1555036	1544069	1554663
15°	1014579	1009135	1004055
20°	504505	523435	503828
25°	254137	286577	248926
30°	101748	110870	88650
35°	47198	45198	37891
40°	20374	22632	19195
45°	14375	17839	14505
50°	4942	12992	5228
55°	2842	5378	3003
60°	1990	2358	1990
65°	1286	1286	1286
70°	806	537	806
75°	0	355	0
80°	0	0	0
85°	0	0	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 22.5°  
 Vertical Angle: 45°  
 Luminance: 17839 cd/sqm



TEST NUMBER: P771094

CATALOG NUMBER: LD6D75BD010-EU6DR3070959035-6LBDP1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	2123.5	28.3
10°-20°	3419.9	45.5
20°-30°	1477.8	19.7
30°-40°	336.8	4.5
40°-50°	115.7	1.5
50°-60°	28.2	0.4
60°-70°	7.3	0.1
70°-80°	0.8	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	7021.2	93.5
0°-40°	7358.0	98.0
0°-60°	7501.9	99.9
0°-90°	7510.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7510.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	24148	24148	24148	24148	24148	
5°	23366	23343	23339	23387	23367	2125
15°	12803	12649	12735	12693	12670	3428
25°	3009	3123	3393	3043	2947	1440
35°	505	516	484	480	406	343
45°	133	165	165	165	134	94
55°	21	22	40	24	22	21
65°	7	7	7	7	7	7
75°	0	0	1	0	0	1
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P771094

CATALOG NUMBER: LD6D75BD010-EU6DR3070959035-6LBDP1MW

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	24148.4	24148.4	24148.4	24148.4	24148.4
2.5°	23988.3	23971.7	23981.2	23993.1	23997.8
5°	23365.9	23343.3	23338.6	23387.2	23367.1
7.5°	22110.3	22078.3	22029.7	22140.0	22243.1
10°	20007.1	19971.5	19866.0	19918.1	20002.3
12.5°	16902.0	16787.0	16784.6	16950.6	16928.0
15°	12803.3	12649.2	12734.6	12693.1	12670.5
17.5°	8609.9	8550.6	8664.4	8630.0	8481.8
20°	6193.6	6209.0	6426.0	6316.9	6185.3
22.5°	4519.5	4575.2	4832.5	4551.5	4448.4
25°	3009.1	3122.9	3393.2	3043.4	2947.4
27.5°	1850.7	1902.9	2176.8	1827.0	1774.8
30°	1151.2	1125.1	1254.4	1076.5	1003.0
32.5°	755.2	722.0	763.5	685.3	626.0
35°	505.1	515.7	483.7	480.2	405.5
37.5°	315.4	362.8	320.1	341.5	260.8
40°	203.9	263.2	226.5	250.2	192.1
42.5°	167.2	202.7	186.1	198.0	170.7
45°	132.8	164.8	164.8	164.8	134.0
47.5°	73.5	110.3	141.1	112.6	78.2
50°	41.5	55.7	109.1	58.1	43.9
52.5°	28.5	32.0	74.7	33.2	29.6
55°	21.3	22.5	40.3	23.7	22.5
57.5°	16.6	17.8	21.3	17.8	16.6
60°	13.0	13.0	15.4	14.2	13.0
62.5°	9.5	9.5	10.7	9.5	9.5
65°	7.1	7.1	7.1	7.1	7.1
67.5°	3.6	4.7	4.7	4.7	4.7
70°	3.6	2.4	2.4	2.4	3.6
72.5°	2.4	1.2	1.2	1.2	1.2
75°	0.0	0.0	1.2	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report







— 0°-180°    - - 45°-225°    - - - - 90°-270°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)