

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P771560

Luminaire Tested: LD6D75BD010-EU6DR6070959035-6LBDP1H

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P771560
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D75BD010-EU6DR6070959035-6LBDP1H
Description: 6 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8645.6 lumens
Efficiency: N/A
Efficacy: 119.4 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 72.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P771560
CATALOG NUMBER: LD6D75BD010-EU6DR6070959035-6LBDP1H

Luminous Intensity Polar Plot





TEST NUMBER: P771560
 CATALOG NUMBER: LD6D75BD010-EU6DR6070959035-6LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93																			
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86																			
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80																			
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70																			
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66																			
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62																			
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59																			
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55																			
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1121857
5°	1149438
10°	1163327
15°	1108222
20°	977111
25°	790316
30°	534580
35°	267886
40°	43459
45°	42539
50°	43379
55°	44041
60°	45256
65°	46303
70°	47375
75°	47956
80°	46247
85°	38486

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 75°
 Luminance: 47956 cd/sqm



TEST NUMBER: P771560

CATALOG NUMBER: LD6D75BD010-EU6DR6070959035-6LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1001.6	11.6
10°-20°	2710.0	31.3
20°-30°	2915.7	33.7
30°-40°	1267.4	14.7
40°-50°	212.9	2.5
50°-60°	207.0	2.4
60°-70°	177.1	2.0
70°-80°	118.5	1.4
80°-90°	35.4	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6627.4	76.7
0°-40°	7894.8	91.3
0°-60°	8314.6	96.2
0°-90°	8645.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8645.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	10268	
5°	10480	###
15°	9797	2710
25°	6556	2916
35°	2008	1267
45°	275	213
55°	231	207
65°	179	177
75°	114	118
85°	31	35
90°	0	



TEST NUMBER: P771560

CATALOG NUMBER: LD6D75BD010-EU6DR6070959035-6LBDP1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	10267.7
2.5°	10556.3
5°	10480.1
7.5°	10504.2
10°	10485.5
12.5°	10269.0
15°	9797.3
17.5°	9163.9
20°	8403.6
22.5°	7589.9
25°	6555.6
27.5°	5243.4
30°	4237.2
32.5°	3265.8
35°	2008.4
37.5°	859.2
40°	304.7
42.5°	280.6
45°	275.3
47.5°	265.9
50°	255.2
52.5°	243.2
55°	231.2
57.5°	219.1
60°	207.1
62.5°	193.8
65°	179.1
67.5°	164.4
70°	148.3
72.5°	131.0
75°	113.6
77.5°	93.5
80°	73.5
82.5°	52.1
85°	30.7
87.5°	10.7
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)