

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P771718

Luminaire Tested: LD6D75BD010-EU6DR7070959035-6LBDP1MW

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P771718
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D75BD010-EU6DR7070959035-6LBDP1MW
Description: 6 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6797.2 lumens
Efficiency: N/A
Efficacy: 93.9 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 72.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P771718
CATALOG NUMBER: LD6D75BD010-EU6DR7070959035-6LBDP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P771718

CATALOG NUMBER: LD6D75BD010-EU6DR7070959035-6LBDP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	834982
5°	810170
10°	787585
15°	777247
20°	725798
25°	545250
30°	385442
35°	136531
40°	71786
45°	76471
50°	79176
55°	80673
60°	81181
65°	79447
70°	74977
75°	69486
80°	61662
85°	50020

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 81198 cd/sqm



TEST NUMBER: P771718

CATALOG NUMBER: LD6D75BD010-EU6DR7070959035-6LBDP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	696.7	10.3
10°-20°	1911.1	28.1
20°-30°	2104.8	31.0
30°-40°	804.2	11.8
40°-50°	379.7	5.6
50°-60°	377.5	5.6
60°-70°	302.2	4.4
70°-80°	173.7	2.6
80°-90°	47.2	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4712.7	69.3
0°-40°	5516.8	81.2
0°-60°	6274.1	92.3
0°-90°	6797.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6797.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7642	
5°	7387	697
15°	6871	1911
25°	4523	2105
35°	1024	804
45°	495	380
55°	424	378
65°	307	302
75°	165	174
85°	40	47
90°	0	



TEST NUMBER: P771718

CATALOG NUMBER: LD6D75BD010-EU6DR7070959035-6LBDP1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	7642.1
2.5°	7562.2
5°	7386.8
7.5°	7240.4
10°	7098.8
12.5°	6979.0
15°	6871.3
17.5°	6611.2
20°	6242.2
22.5°	5446.0
25°	4522.8
27.5°	3937.2
30°	3055.1
32.5°	1973.4
35°	1023.6
37.5°	553.0
40°	503.3
42.5°	499.7
45°	494.9
47.5°	484.0
50°	465.8
52.5°	445.3
55°	423.5
57.5°	399.3
60°	371.5
62.5°	340.0
65°	307.3
67.5°	271.0
70°	234.7
72.5°	198.4
75°	164.6
77.5°	129.5
80°	98.0
82.5°	69.0
85°	39.9
87.5°	15.7
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)