

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P773171

Luminaire Tested: LD6D85BD010-EU6DR6570959027-6LBDP1B

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P773171  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD6D85BD010-EU6DR6570959027-6LBDP1B  
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 65° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6519.0 lumens  
Efficiency: N/A  
Efficacy: 74.3 lumens/watt  
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 87.7  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



Downlight

TEST NUMBER: P773171  
CATALOG NUMBER: LD6D85BD010-EU6DR6570959027-6LBDP1B

### Luminous Intensity Polar Plot





TEST NUMBER: P773171

CATALOG NUMBER: LD6D85BD010-EU6DR6570959027-6LBDP1B

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93																			
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87																			
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80																			
4	97	89	84	79	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	83	78	73	90	83	77	73	81	76	72	79	75	72	77	74	71	69																			
6	87	78	72	68	86	77	72	68	76	71	67	74	70	67	73	69	66	65																			
7	83	73	67	63	81	73	67	63	71	66	62	70	66	62	69	65	62	60																			
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	57																			
9	75	65	59	55	74	65	59	55	64	58	55	63	58	55	62	58	54	53																			
10	71	61	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	701279
5°	701863
10°	726565
15°	727771
20°	670034
25°	570905
30°	437043
35°	308768
40°	182252
45°	73999
50°	26823
55°	14934
60°	8566
65°	4705
70°	4952
75°	3842
80°	4027
85°	3385

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 73999 cd/sqm



TEST NUMBER: P773171

CATALOG NUMBER: LD6D85BD010-EU6DR6570959027-6LBDP1B

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	618.0	9.5
10°-20°	1782.8	27.3
20°-30°	2139.0	32.8
30°-40°	1437.4	22.1
40°-50°	430.3	6.6
50°-60°	75.9	1.2
60°-70°	21.6	0.3
70°-80°	10.6	0.2
80°-90°	3.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4539.8	69.6
0°-40°	5977.2	91.7
0°-60°	6483.5	99.5
0°-90°	6519.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6519.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	6418	
5°	6399	618
15°	6434	1783
25°	4736	2139
35°	2315	1437
45°	479	430
55°	78	76
65°	18	22
75°	9	11
85°	3	3
90°	0	



TEST NUMBER: P773171

CATALOG NUMBER: LD6D85BD010-EU6DR6570959027-6LBDP1B

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	6418.4
2.5°	6445.8
5°	6399.3
7.5°	6495.9
10°	6548.8
12.5°	6536.1
15°	6433.9
17.5°	6184.0
20°	5762.6
22.5°	5266.4
25°	4735.6
27.5°	4136.4
30°	3464.1
32.5°	2854.9
35°	2314.9
37.5°	1781.3
40°	1277.8
42.5°	834.6
45°	478.9
47.5°	253.6
50°	157.8
52.5°	109.5
55°	78.4
57.5°	56.5
60°	39.2
62.5°	25.5
65°	18.2
67.5°	16.4
70°	15.5
72.5°	11.9
75°	9.1
77.5°	8.2
80°	6.4
82.5°	4.6
85°	2.7
87.5°	1.8
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)