

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P771650

Luminaire Tested: LD6D75BD010-EU6DR6570959040-6LBDP1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P771650
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D75BD010-EU6DR6570959040-6LBDP1B
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5890.2 lumens
Efficiency: N/A
Efficacy: 81.4 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 72.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P771650
CATALOG NUMBER: LD6D75BD010-EU6DR6570959040-6LBDP1B

Luminous Intensity Polar Plot





TEST NUMBER: P771650
 CATALOG NUMBER: LD6D75BD010-EU6DR6570959040-6LBDP1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93																			
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87																			
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80																			
4	97	89	84	79	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	83	78	73	90	83	77	73	81	76	72	79	75	72	77	74	71	69																			
6	87	78	72	68	86	77	72	68	76	71	67	74	70	67	73	69	66	65																			
7	83	73	67	63	81	73	67	63	71	66	62	70	66	62	69	65	62	60																			
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	57																			
9	75	65	59	55	74	65	59	55	64	58	55	63	58	55	62	58	54	53																			
10	71	61	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	633636
5°	634159
10°	656480
15°	657572
20°	605398
25°	515835
30°	394892
35°	278983
40°	164680
45°	66860
50°	24239
55°	13506
60°	7736
65°	4266
70°	4472
75°	3462
80°	3649
85°	3134

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 66860 cd/sqm



TEST NUMBER: P771650

CATALOG NUMBER: LD6D75BD010-EU6DR6570959040-6LBDP1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	558.4	9.5
10°-20°	1610.8	27.3
20°-30°	1932.6	32.8
30°-40°	1298.8	22.1
40°-50°	388.8	6.6
50°-60°	68.6	1.2
60°-70°	19.5	0.3
70°-80°	9.5	0.2
80°-90°	3.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4101.9	69.6
0°-40°	5400.7	91.7
0°-60°	5858.1	99.5
0°-90°	5890.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5890.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5799	
5°	5782	558
15°	5813	1611
25°	4279	1933
35°	2092	1299
45°	433	389
55°	71	69
65°	16	20
75°	8	10
85°	2	3
90°	0	



TEST NUMBER: P771650
CATALOG NUMBER: LD6D75BD010-EU6DR6570959040-6LBDP1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	5799.3
2.5°	5824.0
5°	5782.0
7.5°	5869.3
10°	5917.1
12.5°	5905.6
15°	5813.3
17.5°	5587.5
20°	5206.7
22.5°	4758.4
25°	4278.8
27.5°	3737.3
30°	3130.0
32.5°	2579.5
35°	2091.6
37.5°	1609.5
40°	1154.6
42.5°	754.1
45°	432.7
47.5°	229.1
50°	142.6
52.5°	98.9
55°	70.9
57.5°	51.1
60°	35.4
62.5°	23.1
65°	16.5
67.5°	14.8
70°	14.0
72.5°	10.7
75°	8.2
77.5°	7.4
80°	5.8
82.5°	4.1
85°	2.5
87.5°	1.6
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)